

T12 Fluorescent Lamps

Slimline, Slimline "Long Life," Slimline 800,

Nom. Lamp Watts	Product Number	Symbols, Footnotes	Ordering Code	Pkg. Qty. *	Description	Nom. Length (In.)	Rated Avg. Life, Hrs. (202)	Approx. Initial Lumens (203, 204)	Design Lumens (208)	CRI
Slimline Fluorescent Lamps T12 Single Pin Linear Fluorescent Lamps; Instant Start										
30	14140-8	\$	F36T12/CW	24	Cool White, 4100K	36	7500	1850	1630	62
	36609-6	\$	F48T12/SPEC41/EW/ALTO	15	SPEC41, 4100K	48	9000	2575	2350	70
	38700-1	\$	F48T12/CW/EW/ALTO	15	Cool White, 4100K	48	9000	2400	2150	62
39	36613-8		F48T12/SPEC35/ALTO	15	SPEC35, 3500K	48	9000	3000	2800	73
	36219-4		F48T12/D/ALTO	15	Daylight, 6500K	48	9000	2500	220	79
	38702-7		F48T12/CW/ALTO	30	Cool White, 4100K	48	9000	2950	2600	62
	36660-9		F48T12/WW/ALTO	15	Warm White, 3000K	48	9000	2950	2650	53
50	35564-4		F60T12/D	15	Daylight, 6500K	60	12,000	3150	2850	79
	35563-6		F60T12/CW	15	Cool White, 4100K	60	12,000	3450	3050	62
51	35577-6		F64T12/D	15	Daylight, 6500K	64	12,000	3200	2800	79
	35576-8		F64T12/CW	15	Cool White, 4100K	64	12,000	3750	3050	62
56	36614-6		F72T12/30U/ALTO	15	Ultralume, 3000K	72	12,000	4850	4550	85
	36618-7		F72T12/35U/ALTO	15	Ultralume, 3500K	72	12,000	4850	4550	85
	36621-1		F72T12/41U/ALTO	15	Ultralume, 4100K	72	12,000	4850	4550	85
	36623-7		F72T12/SPEC35/ALTO	15	SPEC35, 3500K	72	12,000	4700	4400	73
	36985-0		F72T12/D/ALTO	15	Daylight, 6500K	72	12,000	3800	3350	79
	36989-2		F72T12/CW/ALTO	15	Cool White, 4100K	72	12,000	4450	3900	62
	36661-7		F72T12/WW/ALTO	15	Warm White, 3000K	72	12,000	4550	4000	53
Slimline "Long Life" Fluorescent Lamps T12 Single Pin Linear Fluorescent Lamps; Instant Start										
60	14747-0		F96T12/CW/EW/LL/ALTO	15	Cool White, 4100K	96	15,000	5400	4750	62
	14748-8		F96T12/841/EW/LL/ALTO	15	TL841, 4100K	96	15,000	5900	5550	85
Slimline 800 Series Fluorescent Lamps T12 Single Pin Linear Fluorescent Lamps; Instant Start										
60	14269-5		F96T12/830/EW/ALTO	15	TL830, 3000K	96	12,000	5900	5550	85
	14270-3		F96T12/835/EW/ALTO	15	TL835, 3500K	96	12,000	5900	5550	85
	14271-1		F96T12/841/EW/ALTO	15	TL841, 4100K	96	12,000	5900	5550	85
	14272-9		F96T12/850/EW/ALTO	15	TL850, 5000K	96	12,000	5800	5450	85
Slimline Fluorescent Lamps T12 Single Pin Linear Fluorescent Lamps; Instant Start										
60	36624-5	X \$	F96T12/30U/EW/ALTO	15	Ultralume, 3000K	96	12,000	5900	5550	85
	36625-2	X \$	F96T12/35U/EW/ALTO	15	Ultralume, 3500K	96	12,000	5900	5550	85
	36627-8	X \$	F96T12/41U/EW/ALTO	15	Ultralume, 4100K	96	12,000	5900	5550	85
	36628-6	X \$	F96T12/50U/EW/ALTO	15	Ultralume, 5000K	96	12,000	5850	5500	85
	36630-2	X \$	F96T12/SPEC30/EW/ALTO	15	SPEC30, 3000K	96	12,000	5750	5400	70
	26018-2	X \$	F96T12/SPEC35/EW/ALTO	15	SPEC35, 3500K	96	12,000	5750	5400	73
	26022-4	X \$	F96T12/SPEC41/EW/ALTO	15	SPEC41, 4100K	96	12,000	5750	5400	70
	34198-2	X \$	F96T12/C50/EW	15	Colortone 50, 5000K	96	12,000	4100	3700	92
	36654-2		F96T12/DX/EW/ALTO	15	Daylight Deluxe, 6500K	96	12,000	4200	3675	84
	25840-0		F96T12/CW/EW/ALTO	15	Cool White, 4100K	96	12,000	5400	4750	62
	36656-7		F96T12/WW/EW/ALTO	15	Warm White, 3000K	96	12,000	5500	4850	53
	36655-9	X	F96T12/LW/EW/ALTO	15	Lite White, 4200K	96	12,000	5600	4950	51
	Slimline "Long Life" Fluorescent Lamps T12 Single Pin Linear Fluorescent Lamps; Instant Start									
75	14749-6		F96T12/841/LL/ALTO	15	TL841, 4100K	96	15,000	6600	6225	85
Slimline 800 Series Fluorescent Lamps T12 Single Pin Linear Fluorescent Lamps; Instant Start										
75	14273-7		F96T12/830/ALTO	15	TL830, 3000K	96	12,000	6600	6225	85
	14274-5		F96T12/835/ALTO	15	TL835, 3500K	96	12,000	6600	6225	85
	14275-2		F96T12/841/ALTO	15	TL841, 4100K	96	12,000	6600	6225	85
	14276-0		F96T12/850/ALTO	15	TL850, 5000K	96	12,000	6500	6125	85
Slimline Fluorescent Lamps T12 Single Pin Linear Fluorescent Lamps; Instant Start										
75	36633-6	X	F96T12/30U/ALTO	15	Ultralume, 3000K	96	12,000	6600	6225	85
	36634-4	X	F96T12/35U/ALTO	15	Ultralume, 3500K	96	12,000	6600	6225	85
	36635-1	X	F96T12/41U/ALTO	15	Ultralume, 4100K	96	12,000	6600	6225	85
	36636-9	X	F96T12/50U/ALTO	15	Ultralume, 5000K	96	12,000	6500	6125	85
	36647-6	X	F96T12/SPEC30/ALTO	15	SPEC30, 3000K	96	12,000	6425	6050	70
	36648-4	X	F96T12/SPEC35/ALTO	15	SPEC35, 3500K	96	12,000	6425	6050	73
	36650-0	X	F96T12/SPEC41/ALTO	15	SPEC41, 4100K	96	12,000	6425	6050	70
	34170-1		F96T12/C50	15	Colortone 50, 5000K	96	12,000	4650	4200	92
	34165-1	X	F96T12/N	15	Natural, 3700K	96	12,000	4300	3850	90
	37282-1		F96T12/DX/ALTO	15	Daylight Deluxe, 6500K	96	12,000	4500	3950	84

For the most current product information, go to the e-catalog on www.philips.com Fluorescent symbols and footnotes located on page 87

□ This product utilizes ALTO® Lamp Technology X No longer manufactured, available until inventory depleted