

Nom. Lamp Watts	Product Number	Symbols, Footnotes	Ordering Code	Pkg. Qty. •	Description	Nom. Length (In.)	Rated Avg. Life, Hrs. (202)	Rated Avg. Life, Years (240)	Approx. Initial Lumens (203, 204)	Design Lumens (208)	CRI
<b>HomeLight T12 Fluorescent Lamps</b> Individually Sleeved Fluorescent Lamps; Medium Bipin											
14	14150-7		F14T12/Soft White	6/1	3000K	15	9000	4	700	560	85
15	14146-5		F15T12/Soft White	6/1	3000K	18	9000	4	800	720	85
	14148-1		F15T12/Cool White Plus	6/1	4100K	18	9000	4	800	695	62
20	39120-1	ALTO	F20T12/Soft White	6/1	3000K	24	9000	4	1350	1215	85
	39209-2	ALTO	F20T12/Cool White Plus	6/1	4100K	24	9000	4	1200	1050	62
	39230-8		F20T12/Natural Sunshine	6/1	5000K	24	9000	4	850	755	92
	39233-2	ALTO	F20T12/DayDLX	6/1	6500K	24	9000	4	1075	960	79
	39224-1		F20T12/Blacklight	6/1	—	24	9000	—	—	—	—
	39227-4		F20T12/Plant	6/1	—	24	9000	—	600	—	—
30	39215-9	ALTO	F30T12/Soft White	6/1	3000K	36	18,000	7	2400	2160	85
	39109-4	ALTO	F30T12/Cool White Plus	6/1	4100K	36	18,000	7	2250	1900	62
40	39121-9	ALTO	F40T12/Soft White	6/1	3000K	48	20,000	7	3300	2970	85
	14751-2	ALTO	F40T12/Soft White	6/2	3000K	48	20,000	7	3300	2970	85
	39240-7	ALTO	F40T12/Soft White/15/2PK	15/2	3000K	48	20,000	7	3300	2970	85
	39217-5	ALTO	F40T12/Soft White/84/2PK	84/2	3000K	48	20,000	7	3300	2970	85
	39111-0	ALTO	F40T12/Cool White Plus	6/1	4100K	48	20,000	7	3200	2880	70
	22606-8	ALTO	F40T12/Cool White Plus	10	4100K	48	20,000	7	3200	2880	70
	39239-9	ALTO	F40T12/Cool White Plus/15/2PK	15/2	4100K	48	20,000	7	3200	2880	70
	39211-8	ALTO	F40T12/Cool White Plus/84/2PK	84/2	4100K	48	20,000	7	3200	2880	70
	39231-6	ALTO	F40T12/Natural Sunshine	6/1	5000K	48	20,000	7	2200	1915	92
	29491-8	ALTO	F40/HL EVERYWHERE	15/2	5000K	48	20,000	7	2200	1800	89
	39234-0	ALTO	F40T12/DayDLX	6/1	6500K	48	20,000	7	2325	2025	84
	38752-2	ALTO	F40T12/DayDLX	10	6500K	48	20,000	7	2325	2025	84
	39241-5	ALTO	F40T12/DayDLX/15/2PK	15/2	6500K	48	20,000	7	2325	2025	84
	39123-5	ALTO	F40T12/DayDLX/84/2PK	84/2	6500K	48	20,000	7	2325	2025	84
60	39225-8		F40T12/Blacklight	6/1	—	48	20,000	—	—	—	—
	39228-2		F40T12/Plant	6/1	—	48	20,000	—	1600	—	—
60	20523-7	ALTO	F96T12/CW/EW/8/2PK	8/2	4100K	96	12,000	5	5400	4750	62
	13349-6	ALTO	F96T12/CW/EW/36/2PK	8/2	4100K	96	12,000	5	5400	4750	62
75	37663-2	ALTO	F96T12/DayDLX/8/2PK	8/2	6500K	96	12,000	5	4500	3950	84

**HomeLight Circline Fluorescent Lamps** T9 Circular 4-Pin Fluorescent Lamps

22	39222-5		FC8T9/Soft White	12/1	3000K	8 OD	12,000	4	1150	875	85
	39116-9		FC8T9/Cool White Plus	12/1	4100K	8 OD	12,000	4	1050	775	62
	39235-7		FC8T9/DayDLX	12/1	6500K	8 OD	12,000	4	910	675	79
32	39122-7		FC12T9/Soft White	12/1	3000K	12 OD	12,000	4	1900	1600	85
	39117-7		FC12T9/Cool White Plus	12/1	4100K	12 OD	12,000	4	1800	1500	62
40	39118-5		FC16T9/Cool White Plus	12/1	4100K	16 OD	12,000	4	2500	1975	62

For the most current product information, go to the e-catalog on [www.philips.com](http://www.philips.com)

Fluorescent symbols and footnotes located on page 87

This product utilizes ALTO® Lamp Technology

