



Rocelco 18U Rack with LCD Control Panel

- ✓ *Now with LCD Thermostat Control Panel to automatically set cooling fan start and stop temperature.*
- ✓ *Conforms to all industry standards for 19" audio/video & server racks in 600x600mm configuration.*
- ✓ *Supplied in 3 cartons as flat packed kit to save on freight and storage, which also makes it easier to move to installation location and assemble on site.*
- ✓ *Assembled dimensions HWD 39.4" x 23.6" x 23.6". Max. load capacity 600kg/1320 lbs.*
- ✓ *Complete rack includes frame, all vertical & horizontal rails, front glass door, rear metal door, 2 side panels, 4 braked castors, 2 locks w/2 keys, 2 UL listed fans, assembly hardware & instructions (assembly instructions also on www.rocelco.com). Shelves not included.*
- ✓ *Racks available fully assembled at extra cost.*
- ✓ *Available shelves include 2U 16", 2U 18", 5U 20".*
- ✓ *Other available accessories include 2U blank panels, Rocelco PDU (8-outlet power strip for racks) & Rocelco RCM (rack cable manager).*

