



PRODUCT-DETAILS

15506

HEX DIE W/ DIE CODE 87H BRN



Product image
not available

General Information

Extended Product Type	15506
Product ID	7TAA131880R0002
EAN	5414363138228
Catalog Description	HEX DIE W/ DIE CODE 87H BRN
Long Description	Die for TBM12PCR-LI, TBM14CR-LI and TBM15CR-LI Tools for 500 kcmil Copper, 350 kcmil Aluminum, Die Color Brown, Die Code 87H

Ordering

EAN	5414363138228
Replacement Product ID (NEW)	7TAA131870R0015

Dimensions

Product Net Weight	.4 lb 181.406 g
--------------------	--------------------

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	5 in 127 mm

Package Level 1 Height	1.25 in 32 mm
Package Level 1 Depth / Length	5 in 127 mm
Package Level 2 Units	10 piece
Package Level 2 Width	4.25 in 108 mm
Package Level 2 Height	5.5 in 140 mm
Package Level 2 Depth / Length	7.75 in 197 mm

Additional Information

Brand / Label	Application Tooling
Number of Batteries	0
Product Name	METAL FORMING DIE
Product Type	Die
UPC	786210155067

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	15506
Instructions and Manuals	15506

Classifications

UNSPSC	27112820
IDEA Granular Category Code (IGCC)	2427 >> Lug crimping tool dies

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → WMC Tools



Product image
not available