




Specifications

Width:	3-1/2" (lens) 4.45" (mounting plate) (9.0 cm, 113. cm)
Height:	4-9/20" (11.3 cm)
Depth:	3-57/100" (9.1 cm)
Weight:	1.5 lbs. (0.68 kg)









Catalog Number			
Notes			
Туре			

Hit the Tab key or mouse over the page to see all interactive elements

Introduction

The OVFL 1RH LED security floodlight offers the lowest cost solution for traditional security flood applications.

Delivering 948 lumens at only 13W, OVFL 1RH replaces up to 90W incandescent lamps offering 86% energy savings. The unique compact form is a great alternative to larger sized security luminaires and is ideal for residential, multifamily and multi-use applications requiring an economical solution.

EXAMPLE: OVFL LED 1RH P1 40K 120 DDB

Ordering Information

OVFL LED					
Series	Number of heads	Performance Package	Color Temperature ¹	Voltage	Finish
OVFL LED	1RH 1 head, round	P1 948 lumens	40K 4000K	120 120 volts	DDB Dark Bronze WH White

NOTES

- Correlated color temperature (CCT) shown is nominal per ANSI C78, 377-2008.
- LED lifespan based on IESNA LM-80-08 results and calculated per IESNA TM-21-11 methodology.

FEATURES & SPECIFICATIONS

INTENDED USE

This product is for residential applications. 13W LED wall or ceiling mount security floodlight delivers 948 lumens for an energy-efficient replacement of 90W incandescent security lights. The OVFL LED provides years of maintenance-free general illumination for outdoor applications. Ideal for entrances, walkways, cooridors, yards, driveways and patios.

CONSTRUCTION

Rugged cast-aluminum, corrosion-resistant housing with dark bronze or white polyester powder paint for lasting durability. Diffuse polycarbonate lens is designed for even light distribution and sealed to keep out moisture, dirt and bugs. LEDs maintain 70% of light output at 35,000 hours of service life.

ELECTRICAL

Energy efficient LED provides 948 lumens, consumes 13 input watts utilizing 120V 60Hz driver. Rated for outdoor installations, -40°C minimum ambient.

INSTALLATION

Mounts to a recessed junction box on wall or ceiling. Crossbar and hardware provided. Wet location listed for mounting 4 feet above ground. Adjustable head allows for precise aiming.

LISTINGS

UL/cUL listed Listed to U.S. and Canadian safety standards for wet locations. Tested in accordance with IESNA LM-79 and LM-80 standards.

WARRANTY

One-year limited warranty. Complete warranty terms located at: www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx

Note: Actual performance may differ as a result of end-user environment and application. All values are design or typical values, measured under laboratory conditions at 25 °C. Specifications subject to change without notice.



RESIDENTIAL OUTDOOR

One Lithonia Way • Conyers, Georgia 30012 • Phone: 1-800-705-SERV (7378) • www.lithonia.com © 2010-2020 Acuity Brands Lighting, Inc. All rights reserved.

LEGEND 0.1 fc 0.2 fc 0.5 fc 1.0 fc

