

OptiChannel Fiber Connector OM3, MM

HUBBELL

Features

- Pack of 6 connectors
- Each in a protective capsule with cleave protector, extended dust cap, 900µm boot and splice sleeve
- Compatible with fusion splicers having a removable fiber holder
- Metal holder fixture required (sold separately)
- Hubbell fusion splice heat shrink oven, Catalog Number FCSPHISOVEN is also required for termination



Ordering Information

Description	Color	Catalog Number	UPC Number
Fiber Optic, Connector, Fusion Splice, ST, OM3, Pre-Polished, 900, Pack of 6	Beige	FCSTF900M50G6PK	662620315409

Listings

Telcordia GR-326-CORE
TIA-568-C.3
TIA-604-FOCIS

Performance

Environmental

Operating temperature 0 °C to 70 °C

Optical

Insertion loss 0.5dB (0.35dB typical), 0.75dB max

Mating durability 500 cycles, 0.1dB change

Multimode return loss 35dB Typ, 22dB minimum

Singlemode return loss 55dB Typ, 40dB minimum

Online Resources

Customer Sales Drawings

eCatalog

Installation Instructions

Sales Drawing

