

Pilot and Signaling Devices

Heavy-Duty 30.5 mm Watertight/Oiltight Pilot Devices

Section 9

CR104P

600 Volts Max. AC/DC

10 Amperes Continuous

Suitable for use in NEMA Types 1, 3, 3R, 4, 4X, 12, and 13 applications when mounted in enclosures rates for those same applications. For some NEMA Type 4X applications, protective caps will improve corrosion resistance.

Standard Indicating Lights

Power Supply Type	Supply Voltage	Lamp Type	Product Number ¹
Transformer	120V 50/60 Hz	Incand., 6V, #755	CR104PLG32*
Transformer	200-208V 60 Hz	Incand., 6V, #755	CR104PLG3A*
Transformer	240V 50/60 Hz	Incand., 6V, #755	CR104PLG33*
Transformer	277V 60 Hz	Incand., 6V, #755	CR104PLG3B*
Transformer	347V 60 Hz	Incand., 6V, #755	CR104PLG3C*
Transformer	480V 50/60 Hz	Incand., 6V, #755	CR104PLG34*
Transformer	600V 50/60 Hz	Incand., 6V, #755	CR104PLG35*
Full Voltage	6V 50/60 Hz	Incand., 6V, #755	CR104PLG16*
Full Voltage	12V 50/60 Hz	Incand., 12V, #756	CR104PLG17*
Full Voltage	24V 50/60 Hz	Incand., 24V, #1819	CR104PLG18*
Full Voltage	120V 50/60 Hz	Incand., 130V	CR104PLG22*
Resistor	120V 50/60 Hz	Incand., 60V	CR104PLG42*
Resistor	240V 50/60 Hz	Incand., 130V	CR104PLG43*
Transformer	120V 50/60 Hz	LED, 6V	CR104PLG92*
Transformer	200-208V 60 Hz	LED, 6V	CR104PLG9A*
Transformer	240V 50/60 Hz	LED, 6V	CR104PLG93*
Transformer	277V 60 Hz	LED, 6V	CR104PLG9B*
Transformer	347V 60 Hz	LED, 6V	CR104PLG9C*
Transformer	480V 50/60 Hz	LED, 6V	CR104PLG94*
Transformer	600V 50/60 Hz	LED, 6V	CR104PLG95*
Full Voltage	6 VAC/DC	LED, 6V	CR104PLG86*
Full Voltage	12 VAC/DC	LED, 12V	CR104PLG87*
Full Voltage	24 VAC/DC	LED, 24V	CR104PLG88*
Full Voltage	120 VAC/DC	LED, 120V	CR104PLG82*
Transformer, Flashing	120V 50/60 Hz	Incand., 6V, #267 Flasher	CR104PLG62*
Transformer, Flashing	200-208V 60 Hz	Incand., 6V, #267 Flasher	CR104PLG6A*
Transformer, Flashing	240V 50/60 Hz	Incand., 6V, #267 Flasher	CR104PLG63*
Transformer, Flashing	277V 60 Hz	Incand., 6V, #267 Flasher	CR104PLG6B*
Transformer, Flashing	347V 60 Hz	Incand., 6V, #267 Flasher	CR104PLG6C*
Transformer, Flashing	480V 50/60 Hz	Incand., 6V, #267 Flasher	CR104PLG64*
Transformer, Flashing	600V 50/60 Hz	Incand., 6V, #267 Flasher	CR104PLG65*
Full Voltage, Flashing	6V 50/60 Hz	Incand., 6V, #267 Flasher	CR104PLG56*
Full Voltage	120V	Neon, 120V, #NE51H-R	CR104PLG72*



Standard

Push to Test Indicating Lights

Power Supply Type	Supply Voltage	Lamp Type	Product Number ¹
Transformer	120V 50/60 Hz	Incand., 6V, #755	CR104PLT32*
Transformer	200-208V 60 Hz	Incand., 6V, #755	CR104PLT3A*
Transformer	240V 50/60 Hz	Incand., 6V, #755	CR104PLT33*
Transformer	277V 60 Hz	Incand., 6V, #755	CR104PLT3B*
Transformer	347V 60 Hz	Incand., 6V, #755	CR104PLT3C*
Transformer	480V 50/60 Hz	Incand., 6V, #755	CR104PLT34*
Transformer	600V 50/60 Hz	Incand., 6V, #755	CR104PLT35*
Full Voltage	6V 50/60 Hz	Incand., 6V, #755	CR104PLT16*
Full Voltage	12V 50/60 Hz	Incand., 12V, #756	CR104PLT17*
Full Voltage	24V 50/60 Hz	Incand., 24V, #1819	CR104PLT18*
Full Voltage	120V 50/60 Hz	Incand., 130V	CR104PLT22*
Resistor	120V 50/60 Hz	Incand., 60V	CR104PLT42*
Resistor	240V 50/60 Hz	Incand., 130V	CR104PLT43*
Transformer	120V 50/60 Hz	LED, 6V	CR104PLT92*
Transformer	200-208V 60 Hz	LED, 6V	CR104PLT9A*
Transformer	240V 50/60 Hz	LED, 6V	CR104PLT93*
Transformer	277V 60 Hz	LED, 6V	CR104PLT9B*
Transformer	347V 60 Hz	LED, 6V	CR104PLT9C*
Transformer	480V 50/60 Hz	LED, 6V	CR104PLT94*
Transformer	600V 50/60 Hz	LED, 6V	CR104PLT95*
Full Voltage	6 VAC/DC	LED, 6V	CR104PLT86*
Full Voltage	12 VAC/DC	LED, 12V	CR104PLT87*
Full Voltage	24 VAC/DC	LED, 24V	CR104PLT88*
Full Voltage	120 VAC/DC	LED, 120V	CR104PLT82*
Transformer, Flashing	120V 50/60 Hz	Incand., 6V, #267 Flasher	CR104PLT62*
Transformer, Flashing	200-208V 60 Hz	Incand., 6V, #267 Flasher	CR104PLT6A*
Transformer, Flashing	240V 50/60 Hz	Incand., 6V, #267 Flasher	CR104PLT63*
Transformer, Flashing	277V 60 Hz	Incand., 6V, #267 Flasher	CR104PLT6B*
Transformer, Flashing	347V 60 Hz	Incand., 6V, #267 Flasher	CR104PLT6C*
Transformer, Flashing	480V 50/60 Hz	Incand., 6V, #267 Flasher	CR104PLT64*
Transformer, Flashing	600V 50/60 Hz	Incand., 6V, #267 Flasher	CR104PLT65*
Full Voltage, Flashing	6V 50/60 Hz	Incand., 6V, #267 Flasher	CR104PLT56*
Full Voltage	120V	Neon, 120V, #NE51H-R	CR104PLT72*



Push-to-Test

Lens Colors Available*

Color	Insert in place of asterisk (*)
No Lens	A ^{2,3,4}
Clear ⁴	C ³
Yellow	E ⁴
Green	G ⁴
Blue	L ⁴
Amber	M
Red	R
White	W

²Subtract

³Not suitable for use with LED.

⁴Not suitable for use with NEON light.

¹Replace asterisk (*) in product number with letter from table on right.



Lamps: See page 9-35

Nameplates: See pages 9-40 to 9-41

Technical Data: See pages 9-48 to 9-49

Drilling Plans and Dimensions: See page 9-49