Ultra-slim puck



Thanks to its ¼" profile, our 12V ultra-slim LED puck can be integrated onto any surface. Available as a single unit or as a kit of 3, in both 3000K or 4000K¹. The choice is yours!



Model	Size	Watts	Delivered lumens	LED lumens	CRI	Color °T	Voltage
4006	Ø3.875"	3.6 W	250 lm	300 lm	90	3000 K	12 V
4006-4K [†]	Ø3.875″	3.6 W	250 lm	300 lm	90	4000 K	12 V
4006SQ	3.875"	3.6 W	250 lm	300 lm	90	3000 K	12 V
4006SQ-4K†	3.875"	3.6 W	250 lm	300 lm	90	4000 K	12 V
К4006	3 x Ø3.875"	3.6 W*	250 lm*	300 lm*	90	3000 K	12 V
K4006SQ	3 x 3.875"	3.6 W*	250 lm*	300 lm*	90	3000 K	12 V

[†]White finish only ^{*}Per fixture

Specifications

12V DC LED driver required (4006/4006SQ) Over 50,000 hours of service life 12" input lead with quick connector 24" interconnection harness included Warm white light output Superior LED performance and lifespan Smooth 360° wide spread Minimal heat emission Heat sink and thermal protection JA8 Certified Refer to website for dimmer compatibility 5-year warranty

Note

Plug-in or hard-wired power supply required for installation when purchasing the single unit (4006). Sold separately.

Other Color °T and Finishes available, but may require MOQ's and longer lead times. Please contact your DALS representative for more information.

Power supplies: plug-in

ETR-LED10WPI 12VDC/10W class 2 LED driver

ETR-LED24WPI 12VDC/24W class 2 LED driver

Power supplies: hard-wired

BTO6DIM-IC 6W dimmable LED hardwire driver

BT12DIM-IC 12W dimmable LED hardwire driver

BT24DIM-IC 24W dimmable LED hardwire driver

BT36DIM 36W dimmable LED hardwire driver

BT48DIM

48W dimmable LED hardwire driver

Finish

BK Black (3000K only)
SN Satin Nickel (3000K only)
WH White (3000K, 4000K)

Accessories

4000E-24 24" extension cord


4000E-60 60" extension cord

4000HRNS-24 24" interconnection harness

Order example

4006-SN

4006 round single puck with 250 lumens at 3000K in a satin nickel finish



4006SQ



