Smooth baffle, round

When choosing a recessed fixture, eliminating glare is a priority. The unique positioning of the LED module in this series of downlights will meet that important need.









Model	Size	Watts	Delivered lumens	LED lumens	CRI	Color °T	Voltage
RGR2-3K	2"	8 W	600 lm	750 lm	90	3000 K	120 V
RGR4-3K	4"	14 W	990 lm	1200 lm	90	3000 K	120 V
RGR6-3K	6"	20 W	1600 lm	1900 lm	90	3000 K	120 V

Specifications

Every fixture includes a junction box with integrated dimmable driver Can be daisy chained Superior LED performance and lifespan Regressed light source Minimal heat emission Aluminum construction IC certification (suitable for direct contact with insulation) Air-tight certified as per ASTM E283-04 40° beam angle Suitable for wet locations Refer to website for dimmer compatibility Ideal operating temperature: -20° to 40° C 5-year warranty

Fini	Finish				
\bullet	ВК	Black			



_

Accessories

RFP-UNI Universal rough-in plate

RFP-23

Rough-in plate for 2" and 3" models **RFP-46**

Rough-in plate for 4" and 6" models

Order example

RGR4-3K-BK

Dimmable RGR4-3K 4" round regressed LED fixture in a black finish

Note

Other Color °T and Finishes available, but may require MOQ's and longer lead times. Please contact your DALS representative for more information.

