

SPECIFICATION SHEETS

22WH-BP / 22BLK-BP

OPEN TRIM ALUMINUM HOUSING for BR30 / PAR30 Cyberlite 4.5"



NAME:	
TYPE:	
DATE:	
NOTES:	

SPECIFICATIONS

VOLTAGE: 120V

HOUSING DETAILS:

Its aluminum construction is ideally suited for outdoor installations, such as home soffits.

Each unit comes complete with a mounting plate, mounting clips and an 18" BX cable, for quick connection into a junction box. Built-in thermal protection included.

For use with a PAR30, BR30 style bulb, in either a halogen or LED type.

May be installed in insulated or non-insulated ceilings. For insulated ceilings, use insulated box #IB410 and Vapour Barrier #VP99

This series is available in 4 popular colors; White, Black, Clay or Nugget. This product is sold in contractor packs of 12 units.

ALSO AVAILABLE

Decorative baffle available in either White (BA45WH) or Black (BA45BLK)

CUTTING HOLE:	4.65" (118.1mm)
WARRANTY:	1 year
LAMP:	PAR30/BR30
DIAMETER:	5.80" (147.3mm)
HEIGHT:	5.75" (146.1mm)

APPLICATIONS

The Cyberlite collection is designed for a contractor looking for an affordable solution to recessed lighting. This versatile collection may be used for indoor or outdoor applications. Its aluminum construction is ideally suited for outdoor installations, such as home soffits.




SPECIFICATION SHEETS

22WH-BP / 22BLK-BP

OPEN TRIM ALUMINUM HOUSING for BR30 / PAR30 Cyberlite 4.5"

DIMENSIONS



RATINGS



ORDERING GUIDE

Cyberlite 4.5 inch SERIES

Product Finish
22WHBP-AL White
22BLKBP-AL Black

Notes: Configure product using BOLD options: Ex: 22WHBP-AL