



RZR-CCT-500

SELECTABLE COLOR TEMPERATURE DOWNLIGHT



NAME:	
TYPE:	
DATE:	
NOTES:	

SPECIFICATIONS

LIGHT UNIT:	Aluminum Die cast with powder paint coat preventing discoloring and rusting.	
JUNCTION BOX:	Aluminum extrusion, with knockouts located at each end. Wiring compartment allows for (6) 14 gauge (AWG) insulated conductors. Connection to one (1) downstream unit is pemitted within the junction box compartment. The compartment satisfies junction box volume requirements of CSA C22.2 No. 250.0/UL 1598.	
INSTALLATION:	Ideal for shallow ceiling installations with no housing required. Steel spring clip for easy installation and suitable in t-grid and drop ceiling applications.	
WIRING:	Plenum rated cable used to connect light unit and junction box.	
OPTICS:	EDGE-lit LED technology uses light guided plate to distribute light. A polycarbonate lens is used to provide even illumination throughout the installation. The regressed design offers an anti-glare feature.	
ELECTRICAL & PHASE CONTROL:	Easily connected to a 120V power supply via provided UL recognized driver. Dimming down to 10% with most standard LED dimmers (see list of approved dimmers). Ambient operating temperature: -40°C (-40°F) to +40°C (+104°F). IC, WET Location and AIR-TIGHT rated. Phase Control: Forward Phase. Certifications: This product is ETL listed in USA & Canada, certified to UL standard 1598 and CSA standard C22.2 No. 250.0-08	

CUTTING HOLE:	5.67" (144mm)
MOUNTING PLATE:	MP /AMP / MPHB 500
BEAM ANGLE:	107°
SELECTABLE COLOR TEMPERATURE:	3K - 4K - 5K selectable
CRI:	80
LUMEN OUTPUT:	780 lumens
DIMMABLE:	Yes
WATTS:	11 watts
LED LIFE:	50,000 hours
WARRANTY:	5 years
WIRE CABLE:	FT4 rated
DRIVER (SPECIAL ORDER):	120-277V, 0-10V Dimming

APPLICATIONS

This latest CCT (Correlated Color Temperature) technology is offered in a low-profile design. It features (3) color temperatures 3K, 4K & 5K to select from. The color temperature selector is located on the light unit, which allows for color selection to be made at final install stage. It allows installation in almost any location, even directly under a ceiling joist. Whether it is a Remodel or New Constuction installation, this unit is well suited for indoor / outdoor residential, hospitality, commercial and multifamily applications.








RZR-CCT-500

SELECTABLE COLOR TEMPERATURE DOWNLIGHT

DIMENSIONS







ACCESSORIES



MOUNTING PLATE

Versatile square mounting plate allows for installation of all models of ndr recessed lighting products. refer to our mounting plate compatibility chart to ensure the proper mounting plate is selected.



RAZOR CABLES

These connecting cables are for use with the ndr electric razor series, these cables allow for greater flexibility in designing custom layout needs.



REMODEL VAPOUR BARRIER

The remodel vapour barrier unit may be used with all ndr remodel housings. it is designed to prevent air leakage from your living space into the attic, or any insulated spaces.



ADJUSTABLE MOUNTING PLATE

Versatile adjustable mounting plate allows for installation of all models of ndr recessed lighting products. refer to our mounting plate compatibility chart to ensure the proper mounting plate is selected.



MOUNTING PLATE WITH ADJUSTABLE HANGER BARS

Versatile adjustable mounting plate allows for installation of all models of ndr recessed lighting products. refer to our mounting plate compatibility chart to ensure the proper mounting plate is selected.



VAPOUR BARRIER

This vapour barrier unit may be used with all ndr recessed lighting products. it is designed to prevent air leakage from your living space into the attic, or any insulated spaces.



GOOF RINGS

This goof ring is used when the ceiling hole is wider than the retrofit light unit being installed. refer to our goof ring compatibility chart to ensure the proper goof ring is selected.



SPECIFICATION SHEETS

RZR-CCT-500

SELECTABLE COLOR TEMPERATURE DOWNLIGHT

RATINGS













ORDERING GUIDE

RAZOR 500 CCT SERIES

 Series
 Color Temperature
 Finish

 RZR-CCT-500
 3000K-4000K-5000K/80CRI/11W
 WH White

 3000K-4000K-5000K/80CRI/11W
 BLK Black

 3000K-4000K-5000K/80CRI/11W
 BRZ Bronze

 3000K-4000K-5000K/80CRI/11W
 SC Satin Chrome

Notes: Configure product using BOLD options: Ex: RZR-CCT-500-WH

For 120-277V, (0-10v Dim) Application:

Series Multi-Volt Description

RZR-277V-9/13W 120-277V Driver 0-10V dimming

Notes: Order Driver Model above: (sold separately)