

RZR-CCT-611

REGRESSED DOWNLIGHT WITH SELECTABLE COLOR TEMPERATURE



NAME:	
TYPE:	
DATE:	
NOTES:	

SPECIFICATIONS

	¥
CUTTING HOLE:	6.33"(160.8mm)
MOUNTING PLATE: AMP / MPHB-600	
BEAM ANGLE:	107°
SELECTABLE	3K - 4K - 5K selectable
COLOR EMPERATURE:	
CRI:	80
UMEN OUTPUT:	1170 lumens
DIMMABLE:	Yes
WATTS:	13 watts
LED LIFE:	50,000 hours
WARRANTY:	5 years
WIRE CABLE:	FT6 rated
	120-277V, 0-10V Dimming

APPLICATIONS

This latest CCT (Correlated Color Temperature) technology is offered in a low-profile design. It features three (3) color temperatures 3K, 4K & 5K to select from. The color temperature selector is located on the light unit, which allows for color selection to be made at final install stage. It is IC and AIR-TIGHT rated and allows installation in almost any location, even directly under a ceiling joist. Whether is is a Remodel or New Construction installation, this unit is well suited for indoor / outdoor residential, hospitality, commercial and multifamily applications. It does not require a recessed housing for installation.





SPECIFICATION SHEETS


RZR-CCT-611

REGRESSED DOWNLIGHT WITH SELECTABLE COLOR TEMPERATURE

DIMENSIONS







ACCESSORIES



MOUNTING PLATE

Versatile square mounting plate allows for installation of all models of ndr recessed lighting products. refer to our mounting plate compatibility chart to ensure the proper mounting plate is selected.



RAZOR CABLES

These connecting cables are for use with the ndr electric razor series, these cables allow for greater flexibility in designing custom layout needs.



REMODEL VAPOUR BARRIER

The remodel vapour barrier unit may be used with all ndr remodel housings. it is designed to prevent air leakage from your living space into the attic, or any insulated spaces.



ADJUSTABLE MOUNTING PLATE

Versatile adjustable mounting plate allows for installation of all models of ndr recessed lighting products. refer to our mounting plate compatibility chart to ensure the proper mounting plate is selected.



MOUNTING PLATE WITH ADJUSTABLE HANGER BARS

Versatile adjustable mounting plate allows for installation of all models of ndr recessed lighting products. refer to our mounting plate compatibility chart to ensure the proper mounting plate is selected.



GOOF RINGS

This goof ring is used when the ceiling hole is wider than the retrofit light unit being installed. refer to our goof ring compatibility chart to ensure the proper goof ring is selected.



VAPOUR BARRIER

This vapour barrier unit may be used with all ndr recessed lighting products. it is designed to prevent air leakage from your living space into the attic, or any insulated spaces.



SPECIFICATION SHEETS

RZR-CCT-611

REGRESSED DOWNLIGHT WITH SELECTABLE COLOR TEMPERATURE

RATINGS							
	AIRTIGHT RATED	DIMMABLE	e untertek	Energy JT	IC RATED	WET LOCATIONS	
ORDERING GUID	E						
RAZOR 611 CC	T SERIES						
Series	Color T	emperature			Finish		
RZR-CCT-611	3000K-4000K-5000K/80CRI/13W 3000K-4000K-5000K/80CRI/13W 3000K-4000K-5000K/80CRI/13W 3000K-4000K-5000K/80CRI/13W				WH White BLK Black BRZ Bronze SC Satin Chrome		
Notes:	Configure product usin	ng BOLD options: Ex: RZF	R-CCT-611-WH				
For 120-277V, (0-10v Dim) Applica	tion:					
Series		Multi-Volt Descrip	tion				
RZR-277V-9/13W		120-277V Driver			0-10V dimming		

Order Driver Model above: (sold separately)

Notes:

1.855.739.8228 | www.ndrelectric.com