

YAL4CT38

by Burndy
Catalog ID: YAL4CT38

Prop 65 Notice

Copper HYLUG™, Single Hole w/ Inspection Window, 4 AWG, 3/8" Stud, 8 index, Gray, Short Barrel, Electro- Tin Plated



Product Details

General

| | |
|--------------------------------------|-----------------------------|
| Color Code | Gray |
| Connector Type | Terminal |
| Die Index | 8 |
| Feature - Barrel Style | Chamfered |
| Feature - Barrel Type | Standard |
| Material | Copper |
| Physical Attribute - Number of Holes | 1 |
| Physical Attribute - Tongue Type | Standard |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Temperature Rating | 194 |
| Trade Name | HYLUG™ |
| Type | Standard Barrel, Tin Plated |
| UPC | 781810417539 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - B Length inch | 0.81 in |
| Dimension - Bolt Hole Size inch | 0.39 in |
| Dimension - D inch | 0.83 in |
| Dimension - Hole Size mm | 10 mm |
| Dimension - L Length Overall mm | 50 mm |
| Dimension - Length Overall inch | 1.95 in |
| Dimension - N inch | 0.41 in |
| Dimension - Outside Diameter inch | 0.34 in |
| Dimension - Pad Width inch | 0.58 in |
| Dimension - Stud Size inch | 3/8 |
| Physical Attribute - Tongue Angle | Straight |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |

| | |
|-------------------|-------|
| Voltage - Maximum | 35000 |
|-------------------|-------|

Conductor Related

| | |
|-----------------------------------|--------|
| Conductor - Copper DLO Size Range | N/A |
| Conductor - Copper Str Size | 4 AWG |
| Conductor - Copper Str Size Range | 4 AWG |
| Conductor - Material | Copper |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)