STXH Series

Surge-Trap®

SURGE PROTECTIVE DEVICE

NEMA DEVICES FOR ANSI/UL 1449
TYPE 1 AND 2 APPLICATIONS



The most compact of the STX series offering, the Surge-Trap® Type 1 STXH meets requirements for UL1449 4th Edition and is suitable for any 120/240VAC split phase application. The STXH Series SPD features TPMOV® technology inside making it the safest product available in its category. Its compact size, performance, and reliability are especially ideal for HVAC applications and direct mounting to air condition disconnect switches.

FEATURES AND BENEFITS:

- Designed with the industry-leading Mersen TPMOV® Technology
- Compact footprint designed to mate with AC Disconnect Switches
- LED status indicator (ON = Good, OFF = Replace)
- NEMA 4X enclosure for outdoor or indoor use
- Fits 1/2" knockouts with 18" leads for easy installation
- For use in ANSI/UL Type 1 or 2 SPD installations
- 3 Modes of Protection (L-N, L-L)
- 3-year warranty

RATINGS:

- Volts (U_n): 120V Single Phase, 120/240VAC Split Phase
- Nominal Discharge Current Rating (I_): 20kA
- Surge Capacity (per phase and per mode): 50kA
- Short-Circuit Current Rating (SCCR): 200kA

APPROVALS:

- ANSI/UL 1449 4th Edition, Type 1 SPD, File E210793
- CSA C22.2, Type 1 SPD
- ANSI/IEEE C62.41.1, C62.41.2, C62.45
- UL96A Lightning Protection
- RoHS Compliant









General Product Specif	fications										
Mounting: 1/2" — 14 threaded hub Includes sealing locking washer Wiring: Pre-wired 18" 10AWG Enclosure: NEMA 4X Non-metallic Flammability: UL94-5VA			Operating & Storage Temperature: Relative Humidity Range: Visual End-of-Life Indicator: Frequency:				-40°C to +85°C 0 to 95% non-condensing GREEN = 0K, OUT = REPLACE 50-60Hz				
Catalog Number (includes suffixes*)	System Voltage and Configuration	I _n	Maxim Voltage	Maximum Continuous Operating Voltage (MCOV, U _c)				Voltage Protection Rating (VPR) (UL 1449, 6kV, 3kA)			
			L-N	L-G	L-L	N-G	L-N	L-G	L-L	N-G	
STXH120P05	120V Single Phase (2W)	20kA	150	-	-	-	600	-	-	-	
STXH120P05N	120V Single Phase (2W+G)	20kA	150	300	-	150	600	1000	-	600	
STXH240S05	240/120V Split Phase (3W)	20kA	150	-	300	-	600	-	1000	-	
	Surgo-Trap* XM series LED Blank Indicator On = Producted OFF = Replace Surgo Protective Device TPMO/* Technology ga revenue com				← sid	ible from le profile rough light pe in cover					
Dimensions and Mounting Configurations							Ideal for Air Conditioning Disconnect Applications				
3.22 .13 ————————————————————————————————————							Taxanal Andrews of the Control of th				
3.0	.88	1/2 NPSM	10 AW	'G WIRES			138	Pakres-L Hallmut		**************************************	