

SL1 - Outdoor Diffusion LED Strip

Description

Diffusion SL-1 is a flexible 10mm wide linear LED strip. It is available in 16′ and 32′ rolls that can be cut every 6 LEDs (100mm or 4″).

Features

- Includes endcaps and mounting clips with screws
- Long life LED: 50,000 hrs
- Dimmable with dimming power supply
- 2' power feeds on both ends of every roll
- IP67

Custom lengths available upon request

Specifications

LED: 4.8 W/m (1.5W/ft)Lamp Life: 50,000 hrs LM80LED/Meter: 60/m (18/ft)

• Power Input: 24V DC

• CRI > 91

Lumens

2700K = 394 lm/m (120 lm/ft)

3000K = 416 lm/m (126 lm/ft)

3400K = 438 lm/m (132 lm/ft)

4100K = 460 lm/m (140 lm/ft)

Custom Kelvins available upon request


1 BIN SELECTION

STEP MACADAM ELLIPSE

TEST QUALITY CONTROL







3400 K 4100 K