

# **FEATURES & SPECIFICATIONS**

#### INTENDED USE

Provides years of maintenance-free illumination for outdoor use in residential & commercial applications. Ideal for applications such as lighting walkways and stairways for safety and security.

## CONSTRUCTION

Cast-aluminum housing with corrosion-resistant paint in either dark bronze or white finish.

## ADA compliant.

OPTICS

4000K CCT LEDs.

Polycarbonate lens protects the LED from moisture, dirt and other contaminants.

LUMEN MAINTENANCE: The LED will deliver 70% of its initial lumens at 50,000 hour average LED life. See Lighting Facts label on page 2 for performance details.

#### ELECTRICAL

MVOLT driver operates on any line voltage from 120-277V

Operating temperature -30°C to 40°C.

1KV surge protection standard.

#### INSTALLATION

Surface mounts to universal junction box (provided by others).

## LISTINGS

UL Listed to U.S. and Canadian safety standards for wet locations.

Tested in accordance with IESNA LM-79 and LM-80 standards.

WARRANTY — 5-year limited warranty. Complete warranty terms located at: www.acuitybrands.com/support/customer-support/terms-and-conditions

Note: Actual performance may differ as a result of end-user environment and application.

All values are design or typical values, measured under laboratory conditions at 25 °C. Specifications subject to change without notice.



Catalog Number


Notes


Туре



Specifications

All dimensions are inches (centimeters)





ORDERING INFORMATION For shortest lead times, configure products using <b>bolded options</b> .				Example: OLLWD LED P1 40K MVOLT DDB
Series	Performance Package	Color temperature (CCT)	Voltage	Finish
OLLWD LED Downlight OLLWU LED Up & downlight	P1	<b>40K</b> 4000K	MVOLT 120V-277V   120 120V <sup>1</sup>	DDB Dark bronze WH White <sup>2</sup>

#### Notes

1. Only available with OLLWU and in DDB.

2. Only available with OLLWU.

**Outdoor General Purpose** 


# **OLLWD & OLLWU**


LED WALL CYLINDER LIGHT


## **PHOTOMETRICS**

To see complete photometric reports or download .ies files for this product, visit Lithonia Lighting's Outdoor LED homepage Tested in accordance with IESNA LM-79 and LM-80 standards.


# OLLWD










OLLWU









OLLWU Tighting facts Lithonia Lighting Light Output (Lumens) 947 Watts 14 Lumens per Watt (Efficacy) 67.64 Color Accuracy 70 Light Color 4000 (Bright White) /hite results are according to IESNA LM-76-2008: Approved Method for the Electrical and atometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) veri duct lest data and results. Visit www.lightingfacts.com for the Label Reference Guide. Registration Number: NJSM-Y7HN68 (7/20/2016) Model Number: OLLWU LED P1 40K XXXXX XXX

Type: Luminaire - Other

🜔 LITHONIA LIGHTING

OLLWD-OLLWU