

Charging solutions for every device

Eaton's USB chargers offer fast, convenient and efficient charging of portable electronic devices directly from a standard outlet without bulky adapters or powered computers. This innovative line eliminates clutter in residential and commercial environments while enabling compatibility with USB Type A and C electronics, including smart phones, tablets, e-readers, cameras, MP3 players and more.

Perfect for use in residential, commercial and healthcare applications

- Homes
- · Lounges and coffee houses
- Offices
- OEM applications
- Hotels
- Airports
- Classrooms
 Auditoriums
- Lobbies
- Libraries

Eaton's high powered charging solutions



USB-C charging devices

USB-C duplex receptacle offers fast, convenient and efficient charging of Type-C devices

- · Dual **5A** Type-C charging capacity
- Reversible ports allow for consistent charging regardless of plug-in orientation
- Available in 15A & 20A



USB-A/C charging devices

Quick and easy access for both USB charging and electrical outlets

- · Combination devices offering USB Type-A and Type-C ports
- 5A Type A/C charging capacity
- Available in 15A & 20A



USB-A charging devices

Quick and easy access for both USB charging and electrical outlets

- Dual 3.6A Type-A charging capacity
- Available in 15A & 20A



USB high power charging devices

Combination USB charging devices with TR duplex receptacle

Product description

2-pole, 3-wire grounding 15A, 125V/AC, 5V/DC, 5.0A 20A, 125V/AC, 5V/DC, 5.0A NEMA 5-15R, 5-20R

Design features

- Standard duplex receptacle with one USB-A and C, or two USB-A or two USB-C or one ports rated at a combined 5.0A
- · Dual USB-C charging ports charge most electronic devices that comply with the latest USB-C standard
- Tamper resistant shutters provide compliance with 2017 and 2020 NEC which requires that all 15A and 20A, 125V and 250V, non-locking type receptacles installed in dwelling units must be tamper resistant
- · Automatic grounding system eliminates need for bonding jumper in grounded metal enclosure, provides redundant measure of ground continuity where jumper is used

USB chargers with TR duplex receptacle

- Thermoplastic top and back-body are virtually unbreakable to deliver years of durable performance
- · Steel mounting strap is zinc plated for added corrosion resistance
- Convenient exclusive built-in wire strippers speed installation
- · Replaces a standard duplex receptacle
- Black tamper resistant shutters nearly disappear from view, creating a seamless, contemporary look



TRUSBAC15

TRUSBAC20



TRUSBC15



TRUSBC20



TRUSB5A15



TRUSB5A20







Rating		USB Rating				
Α	V/AC	Α	V/DC	Description	Color suffix	Catalog no.
15	125	5.0	5	USB A/C charger with TR duplex receptacle	B, BK, GY, LA, V, W	☐ TRUSBAC15
20	125	5.0	5	USB A/C charger with TR duplex receptacle	B, BK, GY, LA, V, W	☐ TRUSBAC20
15	125	5.0	5	USB C charger with TR duplex receptacle	B, BK, GY, LA, V, W	☐ TRUSBC15
20	125	5.0	5	USB C charger with TR duplex receptacle	B, BK, GY, LA, V, W	☐ TRUSBC20
15	125	5.0	5	USB 5.0A charger with TR duplex receptacle	B, BK, GY, LA, V, W	☐ TRUSB5A15
20	125	5.0	5	USB 5.0A charger with TR duplex receptacle	B, BK, GY, LA, V, W	☐ TRUSB5A20

cULus Listed UL 498 and UL1310; NOM certified

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White)













Compliances, specifications and availability are subject to change without notice.

USB charging devices

Combination USB charging devices with TR single/duplex receptacle and charging station

Product description

2-pole, 3-wire grounding 15A, 125V/AC, 5V DC 2.4A 15A, 125V/AC, 5V DC 0.7A 15A, 125V/AC, 5V/DC 3.6A; 20A,125V/AC, 5V/DC 3.6A NEMA 5-15R, 5-20R

5V/DC, 5.0A Total (USB charging station) 15A,125V/AC, 5V/DC 3.1A (Hospital Grade Only) 20A,125V/AC, 5V/DC 3.1A (Hospital Grade Only)



- Standard AC receptacle with two USB charging ports for conveniently charging most electronic
- USB-A charging ports rated at 5.0 Amps total -2.5A top two ports, 2.5A bottom two ports (7750 only)
- Dual USB-A charging ports charge most compatible electronic devices with 3.1A or 3.6A total amps
- Tamper resistant shutters provide compliance with 2017 and 2020 NEC which requires that all 15A and 20A, 125V and 250V, non-locking type receptacles installed in dwelling units must be tamper resistant
- · Automatic grounding system eliminates need for bonding jumper in grounded metal enclosure and provides redundant measure of ground continuity where jumper is used

- Thermoplastic top and back-body are virtually unbreakable to deliver years of durable performance
- · Two wipe blade contacts and double wipe ground contacts to ensure long-term plug retention
- Convenient exclusive built-in wire strippers speed installation
- All mounting straps are galvanized (zinc plated)
- · Replaces a standard duplex receptacle and uses a decorator style wallplate
- · Black tamper resistant shutters nearly disappear from view, creating a seamless, contemporary look



TR7765

TR7741

TR7766



TR8355



7750

Combination USB charger with TR receptacle







	USB Rating					
A V/AC A V/DC		V/DC	Description	Color suffix	Catalog no.	
125	0.7	5	Combination USB charger with tamper resistant single receptacle	BK, GY, LA, V, W	☐ TR7740	
125	2.4	5	Combination USB charger with TR single receptacle	B, BK, GY, LA, V, W	☐ TR7741	
125	3.6	5	3.6A USB charger with TR duplex receptacle	B, BK, GY, LA, RB, SG, V, W	□ TR7765	
125	3.6	5	3.6A USB charger with TR duplex receptacle	B, BK, GY, LA, RB, SG, V, W	□ TR7766	
125	3.1	5	USB charger with hospital grade TR duplex receptacle	GY, LA, RD, V, W	☐ TR8255	
125	3.1	5	USB charger with hospital grade TR duplex receptacle	GY, LA, RD, V, W	☐ TR8355	
	125 125 125 125 125 125	125 0.7 125 2.4 125 3.6 125 3.6 125 3.1	125 0.7 5 125 2.4 5 125 3.6 5 125 3.6 5 125 3.1 5	125 0.7 5 Combination USB charger with tamper resistant single receptacle 125 2.4 5 Combination USB charger with TR single receptacle 125 3.6 5 3.6A USB charger with TR duplex receptacle 125 3.6 5 3.6A USB charger with TR duplex receptacle 125 3.1 5 USB charger with hospital grade TR duplex receptacle	125 0.7 5 Combination USB charger with tamper resistant single receptacle 125 2.4 5 Combination USB charger with TR single receptacle B, BK, GY, LA, V, W 125 3.6 5 3.6A USB charger with TR duplex receptacle B, BK, GY, LA, RB, SG, V, W 125 3.6 5 3.6A USB charger with TR duplex receptacle B, BK, GY, LA, RB, SG, V, W 125 3.1 5 USB charger with hospital grade TR duplex receptacle GY, LA, RD, V, W	

cULus Listed UL 498 and UL1310; NOM certified

USB charging station





NOM
426

USB	USB Rating					
Α	V/DC	Description	Color suffix	Catalog no.		
5.0	5	USB multiport charging station	BK, GY, LA, V, W	□ 7750		

UL Listed to UL1310

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: B (Brown), BK (Black), GY (Gray), LA (Light Almond), RB (Oil Rubbed Bronze), RD (Red), SG (Silver Granite), V (Ivory), W (White)

В	вк	GY	LA	RB	RD	SG	V	w
(Brown)	(Black)	(Gray)	(Lt. Almond)	(Oil Rubbed Bronze)	(Red)	(Silver Granite)	(Ivory)	(White)

Compliances, specifications and availability are subject to change without notice.

