

Definite Purpose Controls

Full Voltage Contactors

CR453A, CR353

Standard

Coils and Renewal Parts

25A-150A

AC Replacement Coil

Contactors Prefix	Inductive Amps	Coil Letter Code	Coil Voltage @ 60 Hz	Coil Voltage @ 50 Hz	Product Number
CR453A, CR454A, CR455A	25-40	A	110-120	110-120	55-537283A
CR453A, CR454A, CR455A	25-40	B	208-240	208-240	55-537283B
CR453A, CR454A, CR455A	25-40	C	440-480	380-415	55-537283C
CR453A, CR454A, CR455A	25-40	D	550-600	550-600	55-537283D
CR453A, CR454A, CR455A	25-40	E	12	12	55-537283E
CR453A, CR454A, CR455A	25-40	F	277	—	55-537283F
CR453A, CR454A, CR455A	25-40	H	24	24	55-537283H
CR353A, CR354A, CR355A	25-40	A	110-120	110-120	55-B31A
CR353A, CR354A, CR355A	25-40	B	208-240	208-240	55-B31B
CR353A, CR354A, CR355A	25-40	C	415-480	415-480	55-B31C
CR353A, CR354A, CR355A	25-40	D	575-600	550	55-B31D
CR353A, CR354A, CR355A	25-40	F	277	—	55-B31F
CR353A, CR354A, CR355A	25-40	H (4 pole)	24	24	55-B31H
CR353A, CR354A, CR355A	25-40	H (2-3 pole)	24	24	55-B34H
CR353FE, CR353F, CR354FE, CR354F	50-60	A	110-120	110-120	55-B38A
CR353FE, CR353F, CR354FE, CR354F	50-60	B	208-240	208-240	55-B38B
CR353FE, CR353F, CR354FE, CR354F	50-60	C	440-480	380-415	55-B38C
CR353FE, CR353F, CR354FE, CR354F	50-60	D	575-600	550	55-B38D
CR353FE, CR353F, CR354FE, CR354F	50-60	F	277	—	55-B38F
CR353FE, CR353F, CR354FE, CR354F	50-60	H	24	24	55-B38H
CR355EE, CR355F	50-60	A	110-120	110-120	55-B21A
CR355EE, CR355F	50-60	B	208-240	208-240	55-B21B
CR355EE, CR355F	50-60	C	415-480	415-480	55-B21C
CR355EE, CR355F	50-60	D	575-600	550	55-B21D
CR355EE, CR355F	50-60	F	277	—	55-B21F
CR355EE, CR355F	50-60	H	24	24	55-B21H
CR353EG, CR353H, CR355EG, CR355H	75-90	A	110-120	110-120	55-B22A
CR353EG, CR353H, CR355EG, CR355H	75-90	B	208-240	208-240	55-B22B
CR353EG, CR353H, CR355EG, CR355H	75-90	C	440-480	380-415	55-B22C
CR353EG, CR353H, CR355EG, CR355H	75-90	D	575-600	550	55-B22D
CR353EG, CR353H, CR355EG, CR355H	75-90	F	277	—	55-B22F
CR353EG, CR353H, CR355EG, CR355H	75-90	H	24	24	55-B22H
CR353GJ	120	A	115-120	110	55-501336G002
CR353GJ	120	B	230-240	220	55-501336G003
CR353GJ	120	C	460-480	440	55-501336G004
CR353GJ	120	D	575-600	550	55-501336G005
CR353GK	150	A	115-120	110	55-501563G002
CR353GK	150	B	230-240	220	55-501563G003
CR353GK	150	C	460-480	440	55-501563G004
CR353GK	150	D	575-600	550	55-501563G005

