

Three pole contactors. Screw terminal

Max.oper.current Non-inductive load AC1 A	Motors <440V, 3 ~ 50/60Hz AC3 A	Admissible power AC3				Electrical endurance Cat. AC3 Operations	Aux. contacts		Control circuit: Alternating current		Control circuit: Direct current		Control circuit: Coil with electronic module (AC/DC)	
		220V 230V	380V 400V	415V 440V	500V 440V		•3	•1	Cat. no. (1)	Pack (3)	Cat. no. (1)	Pack (3)	Cat. no. (1)	Pack (3)
		kW HP	kW HP	kW HP	kW HP		•4	•2	Ref. no. see bottom		Ref. no. see bottom		Ref. no. see bottom	
25	9	2.2 3	4 5.5	4 5.5	5.5 7.5	2x10 <sup>6</sup>	1 0	0 0	CL00A310T♦ CL00A301T♦	5 5	CL00D310T♦ CL00D301T♦	10 10	- -	- -
25	12	3 4	5.5 7.5	5.5 7.5	7.5 10	2x10 <sup>6</sup>	1 0	0 1	CL01A310T♦ CL01A301T♦	5 5	CL01D310T♦ CL01D301T♦	10 10	- -	- -
32	18	4 5.5	7.5 10	7.5 10	10 13.5	1.7x10 <sup>6</sup>	1 0	0 1	CL02A310T♦ CL02A301T♦	5 5	CL02D310T♦ CL02D301T♦	10 10	- -	- -
45	25	7.5 10	11 15	11 15	15 20	1.2x10 <sup>6</sup>	0 0	0 0	CL25A300T♦	5	CL25D300T♦	10	-	-
45	25	7.5 10	12 16	12 16	15 20	2x10 <sup>6</sup>	1 0	0 1	CL03A310M♦ CL03A301M♦	10 10	CL03D310M♦ CL03D301M♦	10 10	- -	- -
60	32	9 12	16 22	16 22	18.5 25	2x10 <sup>6</sup>	1 0	0 1	CL04A310M♦ CL04A301M♦	10 10	CL04D310M♦ CL04D301M♦	10 10	- -	- -
60	40	11 15	18.5 25	22 30	25 34	2x10 <sup>6</sup>	0 0	0 0	CL45A300M♦	10	CL45D300M♦	10	-	-
90	50	15 20	22 30	25 34	30 40	1.8x10 <sup>6</sup>	0 0	0 0	CL06A300M♦	1	CL06D300M♦	1	CL06E300M♦	1
110	65	18.5 25	30 40	37 50	40 55	1.7x10 <sup>6</sup>	0 0	0 0	CL07A300M♦	1	CL07D300M♦	1	CL07E300M♦	1
110	80	22 30	37 50	45 60	45 60	1.5x10 <sup>6</sup>	0 0	0 0	CL08A300M♦	1	CL08D300M♦	1	CL08E300M♦	1
140	95	25 34	45 60	50 68	55 75	1.7x10 <sup>6</sup>	0 0	0 0	CL09A300M♦	1	CL09D300M♦	1	CL09E300M♦	1
140	105	30 40	55 75	55 75	65 88	1.5x10 <sup>6</sup>	0 0	0 0	CL10A300M♦	1	CL10D300M♦	1	CL10E300M♦	1
Spare coils						CL00 - CL25			LB1A ♦	5	LB1D ♦	5	-	-
						CL03 - CL45			LB3A ♦	5	LB3D ♦	5	-	-
						CL06 - CL10			LB4A ♦	5	LB4D ♦	1	-	-
						coil + electronic module	CL06E - CL10E						LB4E ♦	1

- (1) To complete the catalogue number, replace the symbol ♦ by the code corresponding to the voltage and frequency of the control circuit (see A.52).
- (2) Equipped with two blocks BCLF
- (3) Multipack, see below

Multipack. Series M and Series CL

To reduce the amount of waste packaging material and to save time during installation, we offer the opportunity to order contactors in a multipack without the individual packaging.

Product	Type	Standard pack	Multipack (1)
Contactors	CL00A...CL25A...	20	40
	CL03...CL45...	10	20

(1) The quantity ordered must be a multiple of the quantity in each multipack (with the same frame/size and coil voltage)

How to order

For reference numbers, see chapter X, pg. X.4

To order a multipack, add the suffix **MP** to the standard catalogue number

Example	Standard pack	Multipack
	CL03A400MJ	CL03A400MJ MP (20 pieces)



Order codes

Intro

A

B

C

D

E

F

G

H

I

J/X