



M12

203-20

203-21



M12™ Heated AXIS™ Jacket Kit

★★★★☆ 3.0 (30) [Write a review](#)

Our M12™ Heated AXIS™ jackets are designed to protect you from the cold and weather elements on the job site. Powered by M12™ REDLITHIUM™ Battery Technology, these heated work jackets use carbon fiber heating elements to create and distribute heat to the chest, back and shoulders. A one-touch LED controller heats up the battery heated jacket to three heat settings, creating a comfortable heat for any environment or weather. This

[Read More](#)

INCLUDES

- (1) M12™ Heated AXIS™ Jacket (203-20)
- (1) M12™ REDLITHIUM™ CP2.0 Battery (48-11-2420)
- (1) M12™ Compact Charger & Power Source

Color - Black



KEY FEATURES

SPECIFICATIONS

REVIEWS

**PORTABLE PRODUCTIVITY
TRADE FOCUSED
SYSTEM WIDE**

- ✓ Quick-heat function reaches selected temperature 3X FASTER
- ✓ One-touch LED controller with (3) heat settings per heat zone
- ✓ Up to (8) hours of run-time with M12™ REDLITHIUM™ 2.0 Compact Battery Pack
- ✓ Heating Zones: Chest, Back, & Shoulders
- ✓ Washer and dryer safe
- ✓ Wind & Water Resistant
- ✓ Compressible design makes layering comfortable and easy.
- ✓ Reinforced high-wear zones protect from abrasion and tears
- ✓ 100% Polyester insulation keeps heat in, doesn't add bulk
- ✓ Adjustable waist with drop tail extended back
- ✓ (2) outer zip pockets, (1) inner zip pocket, (1) low-profile battery pocket

BATTERY SPECIFICATIONS

Voltage	12V
---------	-----

PRODUCT SPECIFICATIONS

Heat Elements	Chest, Back, and Shoulders
Heat Settings	(3) Heat Settings: High, Medium, Low
Power Source	Cordless
Battery System	M12™
Color	Black
Heated Gear Warranty	1 Year

Inner Material	Brushed Tricot
Insulated	Yes
Washing	Washer and Dryer Safe
Weather Resistant	Wind/Water Resistant