

# Tmax XT ranges

## Ordering details XT2

### XT2 125A TMF/TMA - Fixed (F) - 3 poles - Front terminals (F) - UL/CSA

Thermomagnetic trip unit			IC Rating (600V)	N 18 kA		S 22 kA		H 25 kA		L 35 kA		V 42 kA		X 45 kA	
Type	In	I <sub>3</sub>		Part number	Part number	Part number	Part number	Part number	Part number	Part number	Part number	Part number	Part number	Part number	
TMF	15	400	XT2NU3015AFF000XXX	XT2SU3015AFF000XXX	XT2HU3015AFF000XXX	XT2LU3015AFF000XXX	XT2VU3015AFF000XXX	XT2XU3015AFF000XXX							
	20	400	XT2NU3020AFF000XXX	XT2SU3020AFF000XXX	XT2HU3020AFF000XXX	XT2LU3020AFF000XXX	XT2VU3020AFF000XXX	XT2XU3020AFF000XXX							
	25	400	XT2NU3025AFF000XXX	XT2SU3025AFF000XXX	XT2HU3025AFF000XXX	XT2LU3025AFF000XXX	XT2VU3025AFF000XXX	XT2XU3025AFF000XXX							
	30	400	XT2NU3030AFF000XXX	XT2SU3030AFF000XXX	XT2HU3030AFF000XXX	XT2LU3030AFF000XXX	XT2VU3030AFF000XXX	XT2XU3030AFF000XXX							
	35	400	XT2NU3035AFF000XXX	XT2SU3035AFF000XXX	XT2HU3035AFF000XXX	XT2LU3035AFF000XXX	XT2VU3035AFF000XXX	XT2XU3035AFF000XXX							
	40	400	XT2NU3040AFF000XXX	XT2SU3040AFF000XXX	XT2HU3040AFF000XXX	XT2LU3040AFF000XXX	XT2VU3040AFF000XXX	XT2XU3040AFF000XXX							
	50	500	XT2NU3050AFF000XXX	XT2SU3050AFF000XXX	XT2HU3050AFF000XXX	XT2LU3050AFF000XXX	XT2VU3050AFF000XXX	XT2XU3050AFF000XXX							
	60	600	XT2NU3060AFF000XXX	XT2SU3060AFF000XXX	XT2HU3060AFF000XXX	XT2LU3060AFF000XXX	XT2VU3060AFF000XXX	XT2XU3060AFF000XXX							
	70	700	XT2NU3070AFF000XXX	XT2SU3070AFF000XXX	XT2HU3070AFF000XXX	XT2LU3070AFF000XXX	XT2VU3070AFF000XXX	XT2XU3070AFF000XXX							
	TMA	56...80	400...800	XT2NU3080BFF000XXX	XT2SU3080BFF000XXX	XT2HU3080BFF000XXX	XT2LU3080BFF000XXX	XT2VU3080BFF000XXX	XT2XU3080BFF000XXX						
63...90		450...900	XT2NU3090BFF000XXX	XT2SU3090BFF000XXX	XT2HU3090BFF000XXX	XT2LU3090BFF000XXX	XT2VU3090BFF000XXX	XT2XU3090BFF000XXX							
70...100		500...1000	XT2NU3100BFF000XXX	XT2SU3100BFF000XXX	XT2HU3100BFF000XXX	XT2LU3100BFF000XXX	XT2VU3100BFF000XXX	XT2XU3100BFF000XXX							
77...110		550...1100	XT2NU3110BFF000XXX	XT2SU3110BFF000XXX	XT2HU3110BFF000XXX	XT2LU3110BFF000XXX	XT2VU3110BFF000XXX	XT2XU3110BFF000XXX							
87.5...125		625...1250	XT2NU3125BFF000XXX	XT2SU3125BFF000XXX	XT2HU3125BFF000XXX	XT2LU3125BFF000XXX	XT2VU3125BFF000XXX	XT2XU3125BFF000XXX							

3

### XT2 125A TMF/TMA - Fixed (F) - 3 poles - Front terminals (F) - 100% rated UL/CSA

Thermomagnetic trip unit			IC Rating (600V)	NQ 18 kA		SQ 22 kA		HQ 25 kA		LQ 35 kA		VQ 42 kA		XQ 45 kA	
Type	In	I <sub>3</sub>		Part number	Part number	Part number	Part number	Part number	Part number	Part number	Part number	Part number	Part number		
TMF	15	400	XT2NQ3015AFF000XXX	XT2SQ3015AFF000XXX	XT2HQ3015AFF000XXX	XT2LQ3015AFF000XXX	XT2VQ3015AFF000XXX	XT2XQ3015AFF000XXX							
	20	400	XT2NQ3020AFF000XXX	XT2SQ3020AFF000XXX	XT2HQ3020AFF000XXX	XT2LQ3020AFF000XXX	XT2VQ3020AFF000XXX	XT2XQ3020AFF000XXX							
	25	400	XT2NQ3025AFF000XXX	XT2SQ3025AFF000XXX	XT2HQ3025AFF000XXX	XT2LQ3025AFF000XXX	XT2VQ3025AFF000XXX	XT2XQ3025AFF000XXX							
	30	400	XT2NQ3030AFF000XXX	XT2SQ3030AFF000XXX	XT2HQ3030AFF000XXX	XT2LQ3030AFF000XXX	XT2VQ3030AFF000XXX	XT2XQ3030AFF000XXX							
	35	400	XT2NQ3035AFF000XXX	XT2SQ3035AFF000XXX	XT2HQ3035AFF000XXX	XT2LQ3035AFF000XXX	XT2VQ3035AFF000XXX	XT2XQ3035AFF000XXX							
	40	400	XT2NQ3040AFF000XXX	XT2SQ3040AFF000XXX	XT2HQ3040AFF000XXX	XT2LQ3040AFF000XXX	XT2VQ3040AFF000XXX	XT2XQ3040AFF000XXX							
	50	500	XT2NQ3050AFF000XXX	XT2SQ3050AFF000XXX	XT2HQ3050AFF000XXX	XT2LQ3050AFF000XXX	XT2VQ3050AFF000XXX	XT2XQ3050AFF000XXX							
	60	600	XT2NQ3060AFF000XXX	XT2SQ3060AFF000XXX	XT2HQ3060AFF000XXX	XT2LQ3060AFF000XXX	XT2VQ3060AFF000XXX	XT2XQ3060AFF000XXX							
	70	700	XT2NQ3070AFF000XXX	XT2SQ3070AFF000XXX	XT2HQ3070AFF000XXX	XT2LQ3070AFF000XXX	XT2VQ3070AFF000XXX	XT2XQ3070AFF000XXX							
	TMA	56...80	400...800	XT2NQ3080BFF000XXX	XT2SQ3080BFF000XXX	XT2HQ3080BFF000XXX	XT2LQ3080BFF000XXX	XT2VQ3080BFF000XXX	XT2XQ3080BFF000XXX						
63...90		450...900	XT2NQ3090BFF000XXX	XT2SQ3090BFF000XXX	XT2HQ3090BFF000XXX	XT2LQ3090BFF000XXX	XT2VQ3090BFF000XXX	XT2XQ3090BFF000XXX							
70...100		500...1000	XT2NQ3100BFF000XXX	XT2SQ3100BFF000XXX	XT2HQ3100BFF000XXX	XT2LQ3100BFF000XXX	XT2VQ3100BFF000XXX	XT2XQ3100BFF000XXX							

### XT2 125A TMF/TMA - Fixed (F) - 4 poles - Front terminals (F) - UL/CSA

Thermomagnetic trip unit			IC Rating (600V)	N 18 kA		S 22 kA		H 25 kA		L 35 kA		V 42 kA		X 45 kA	
Type	In	I <sub>3</sub>		Part number	Part number	Part number	Part number	Part number	Part number	Part number	Part number	Part number	Part number		
TMF	15	400	XT2NU4015AFF000XXX	XT2SU4015AFF000XXX	XT2HU4015AFF000XXX	XT2LU4015AFF000XXX	XT2VU4015AFF000XXX	XT2XU4015AFF000XXX							
	20	400	XT2NU4020AFF000XXX	XT2SU4020AFF000XXX	XT2HU4020AFF000XXX	XT2LU4020AFF000XXX	XT2VU4020AFF000XXX	XT2XU4020AFF000XXX							
	25	400	XT2NU4025AFF000XXX	XT2SU4025AFF000XXX	XT2HU4025AFF000XXX	XT2LU4025AFF000XXX	XT2VU4025AFF000XXX	XT2XU4025AFF000XXX							
	30	400	XT2NU4030AFF000XXX	XT2SU4030AFF000XXX	XT2HU4030AFF000XXX	XT2LU4030AFF000XXX	XT2VU4030AFF000XXX	XT2XU4030AFF000XXX							
	35	400	XT2NU4035AFF000XXX	XT2SU4035AFF000XXX	XT2HU4035AFF000XXX	XT2LU4035AFF000XXX	XT2VU4035AFF000XXX	XT2XU4035AFF000XXX							
	40	400	XT2NU4040AFF000XXX	XT2SU4040AFF000XXX	XT2HU4040AFF000XXX	XT2LU4040AFF000XXX	XT2VU4040AFF000XXX	XT2XU4040AFF000XXX							
	50	500	XT2NU4050AFF000XXX	XT2SU4050AFF000XXX	XT2HU4050AFF000XXX	XT2LU4050AFF000XXX	XT2VU4050AFF000XXX	XT2XU4050AFF000XXX							
	60	600	XT2NU4060AFF000XXX	XT2SU4060AFF000XXX	XT2HU4060AFF000XXX	XT2LU4060AFF000XXX	XT2VU4060AFF000XXX	XT2XU4060AFF000XXX							
	70	700	XT2NU4070AFF000XXX	XT2SU4070AFF000XXX	XT2HU4070AFF000XXX	XT2LU4070AFF000XXX	XT2VU4070AFF000XXX	XT2XU4070AFF000XXX							
	TMA	56...80	400...800	XT2NU4080BFF000XXX	XT2SU4080BFF000XXX	XT2HU4080BFF000XXX	XT2LU4080BFF000XXX	XT2VU4080BFF000XXX	XT2XU4080BFF000XXX						
63...90		450...900	XT2NU4090BFF000XXX	XT2SU4090BFF000XXX	XT2HU4090BFF000XXX	XT2LU4090BFF000XXX	XT2VU4090BFF000XXX	XT2XU4090BFF000XXX							
70...100		500...1000	XT2NU4100BFF000XXX	XT2SU4100BFF000XXX	XT2HU4100BFF000XXX	XT2LU4100BFF000XXX	XT2VU4100BFF000XXX	XT2XU4100BFF000XXX							
77...110		550...1100	XT2NU4110BFF000XXX	XT2SU4110BFF000XXX	XT2HU4110BFF000XXX	XT2LU4110BFF000XXX	XT2VU4110BFF000XXX	XT2XU4110BFF000XXX							
87.5...125		625...1250	XT2NU4125BFF000XXX	XT2SU4125BFF000XXX	XT2HU4125BFF000XXX	XT2LU4125BFF000XXX	XT2VU4125BFF000XXX	XT2XU4125BFF000XXX							