

# Modular Metering Meter Mod III

## Section 2

Meter Stack Modules—Commercial  
Tenant Main Circuit Breakers

### Tenant Main Circuit Breakers for 200A/225A, 3 Pole Sockets

Amps	10kAIC	Wire Size
15	TEB132015	(1) #14-3 CU; #12-1 AL
20	TEB132020	
25	TEB132025	
30	TEB132030	
35	TEB132035	
40	TEB132040	
45	TEB132045	
50	TEB132050	
60	TEB132060	
70	TEB132070	
80	TEB132080	(1) #6/20 CU; #4-2/0 AL
90	TEB132090	(1) #3-3/0 CU; #1-3/0 AL
100	TEB132100	
125	TQD32125	(1) #1-300 CU; #1-300 AL
150	TQD32150	
175	TQD32175	
200	TQD32200	
225	Use TMQC	

### Tenant Main Circuit Breakers for 200A/225A, 3 Pole Sockets

Amps	22kAIC	Wire Size
100	THQD32100	(1) #1-300 CU; #1-300 AL
125	THQD32125	
150	THQD32150	
175	THQD32175	
200	THQD32200	
225	Use TMQC	—

### Tenant Main Circuit Breakers for 200A/225A, 3 Pole Sockets

Amps	QC 42 kAIC	QF 65 kAIC	QV 100 kAIC	Wire Size
60	TMQC32060	TMQF32060	TMQV32060	#6-4/0 <sup>1</sup>
70	TMQC32070	TMQF32070	TMQV32070	
80	TMQC32080	TMQF32080	TMQV32080	
90	TMQC32090	TMQF32090	TMQV32090	
100	TMQC32100	TMQF32100	TMQV32100	
110	TMQC32110	TMQF32110	TMQV32110	
125	TMQC32125	TMQF32125	TMQV32125	
150	TMQC32150	TMQF32150	TMQV32150	
175	TMQC32175	TMQF32175	TMQV32175	
200	TMQC32200	TMQF32200	TMQV32200	
225	TMQC32225	TMQF32225	TMQV32225	

<sup>1</sup>For 60A-225A 3P breakers use TMQV225L3 to get 300MCM terminals.