PatchLink™ Horizontal Cable Managers



specifications

Horizontal cable managers shall be capable of managing cables on the front and rear of any 19" EIA rack. The manager shall consist of a 1-piece construction that is molded out of plastic. Horizontal managers shall have pass through holes that incorporate integral bend radius control as well as fingers with rounded edges. The manager shall have rigid end fingers that incorporate integral bend radius control. Hinged covers shall allow access to the cable pathway without having to completely remove the cover from the manager.



technical information

Dimensions:

Part Number	RU	Height in. (mm)	Width in. (mm)	Depth in. (mm)	
WMP1E	2	3.5 (88.9)	19.0 (482.6)	8.9 (225.5)	
WMPF1E	2	3.5 (88.9)	19.0 (482.6)	3.7 (93.7)	
WMPH2E	2	3.5 (88.9)	19.0 (482.6)	8.9 (225.5)	
WMPHF2E	2	3.5 (88.9)	19.0 (482.6)	3.7 (93.7)	
WMPSE	1	1.7 (44.1)	19.0 (482.6)	8.9 (225.5)	
WMPFSE	1	1.7 (44.1)	19.0 (482.6)	3.7 (93.7)	
WMPLSE	1	1.7 (44.1)	19.0 (482.6)	7.9 (200.1)	
WMPLFSE	1	1.7 (44.1)	19.0 (482.6)	2.7 (69.1)	

Temperature
rating:Max storage temperature 65°C (149°F);
Max operating temperature 60°C (140°F)

Packaging: Cable managers include hinged cover(s), mounting hardware

key features and benefits

,					
Integral bend radius control	Maintains bend radii as cables transition to and from horizontal and vertical pathway				
Dual hinged cover	Opens upward or downward to provide easy access to cables in horizontal pathway without having to completely remove cover				
Increased finger spacing	Provides larger area for high performance Category 6 cable				
One piece, plastic construction	Provides durability and easy installation				
Flexible fingers	Provide for easy installation and organizes cables simplifyir moves, adds, and changes				
Rounded edges on fingers	Protect cables from snags and damage to cable				
Cable pass through holes	Provide ease of installation and cable maintenance				

applications

Panduit® PatchLink™ Horizontal Cable Managers provide a neat and efficient way to manage patch cables on any EIA 19" rack. They can be used in multimedia applications to manage copper, fiber optic, and coax cables. Flexible fingers organize the patch cords simplifying moves, adds, and changes while the integral bend radius control and "closed" design protects the patch cables in the pathway. All of these

features combine to provide the user with a horizontal cable management solution that simplifies cable routing in a finished, professional appearance. When used with the Panduit® Mini-Com® patch panels, patch cords, vertical cable managers, and racks, the user receives a total system that satisfies functional and aesthetic requirements for telecommunications rooms.

2 RU Managers

Front and Rear, with

bend radius clips: WMPH2E

Front and Rear: WMP1E

Front Only, with

bend radius clips: WMPHF2E

Front Only: WMPF1E

1 RU Managers

Front and Rear:

Front and Rear,

short depth: WMPLSE

WMPSE

WMPFSE

Front Only: Front Only.

short depth: WMPLFSE

Racks

2 post 19"

EIA standard rack: R2P^
4 post rack 7' 30" depth with
#12-24 threaded rails: R4P*^
4 post rack 7' 23" depth with
#12-24 threaded rails: R4P23*^

4 post rack 7' 36" depth with #12-24 threaded rails: R4P36*^

4 post rack 7' 42" depth with #12-24 threaded rails: R4P42*^

Panel Extender Brackets

1 RU: PEB1 **2 RU:** PEB2

Accessories


Cable retainers: WR3E-X

*Add "CN" for Cage Nut Rails

^Add suffix 96 to the end of the part number for 8 foot versions.

www.panduit.com

PatchLink™ Horizontal Cable Managers



All managers have 17" long front covers except for the WMPH2E and WMPHF2E, which have19 3/8" long front covers for complete coverage to vertical managers.

Cable Capacity Chart

Part Number	Front				Rear					
	Channel Area (in²)	Cat. 6A (28 AWG - 0.185")	Cat. 6A (24 AWG - 0.275")	Cat. 6 (28 AWG - 0.150")	Cat. 6 (24 AWG - 0.235")	Channel Area (in²)	Cat. 6A (28 AWG - 0.185")	Cat. 6A (24 AWG - 0.275")	Cat. 6 (28 AWG - 0.150")	Cat. 6 (24 AWG - 0.235")
WMP1E WMPF1E	6.8	101	45	153	62	9.1 -	134 -	60 -	204	83 -
WMPH2E WMPHF2E	6.8	101	45	153	62	9.1 -	134 -	60 -	204 -	83 -
WMPSE WMPFSE	2.7	40	18	61	25	4.6 -	68 -	30 -	104 -	42 -
WMPLSE WMPLFSE	1.7	25	11	38	15	4.6 -	68 -	30 -	104 -	42 -

Dimensions are in inches. (Dimensions in parenthesis are metric.)

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA PANDUIT E Phone: 800.777.3300 London, UK

PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

