



Specification Sheet

THM1SC Harness Mounts

	<p>The Panduit THM1SC Harness Mount with a fir tree push barb holds wire bundles tightly and installs quickly into pre-drilled holes. The mount requires a panel hole diameter of .250" (6.5mm) and panel thickness between .03" to .14" (.9mm to 3.4mm). For use in indoor environments. Made of Nylon 6.6, these come colored as natural (not shown) or in Heat Stabilized black as shown. These come available in packs of 100 or 1000.</p>
---	--

Part Number	Material	Color	Operating Temperature	Package Qty
THM1SC-C	Nylon 6.6	Natural	-76 °F (-60 °C) to 185 °F (85 °C)	100
THM1SC-M				1000
THM1SC-C30	Heat Stabilized	Black	-76 °F (-60 °C) to 239 °F (115 °C)	100
THM1SC-M30	Nylon 6.6			1000

Mount Method: Fir Tree

Environment: Indoor

Hole Size needed: 0.25" ± 0.10" (6.5mm ± 0.25mm)

Panel Thickness: 0.036" to 0.135" (0.9mm to 3.4mm)

Height: 0.74" (18.8mm)

Length: 0.98" (24.9mm)

Width: 0.38" (9.7mm)

Standards: UL Recognized E136577

Flammability: UL94 V-2

For Use With: Miniature, Intermediate, and Standard Cross-Section Ties