

## EJ600 Series 24-Hour or 7-Day In-Wall Timers



- Up to 14 (7 ON/OFF) programmable events per day
- Random setting turns lights ON/OFF at different times so it appears someone is always at their home or business
- Auto Daylight Saving Time adjustment
- Incandescent/Fluorescent/CFL/LED compatible
- Astronomic feature auto adjusts to sunrise/sunset
- Can be used for 24-Hour or 7-Day load control of lights, fans, pumps and other medium-duty loads
- Built-in rechargeable lithium ion battery backup
- Single-pole or 3-way compatible
- For use with decorator-style wall plate (not included)
- Requires neutral wire

Model #	Color
C. EJ600	White
D. EJ600A	Almond

<b>Ratings:</b>	
<b>Input Voltage:</b> 120 VAC, 60 Hz.	<b>Inductive Ballast:</b> 500 VA
<b>General Purpose:</b> 12 A, 120 VAC, 60 Hz.	<b>Motor:</b> 1/2 HP
<b>Resistive (heater):</b> 12 A, 120 VAC, 60 Hz.	<b>Operating Temperature:</b> 32°F to 104°F (0°C to 40°C)
<b>Tungsten (incandescent):</b> 15 A single-gang, 12 A multi-gang	<b>Warranty:</b> Limited 1 year



C.

D.



E.



F.

## EJ351 Programmable 24-Hour Security Timer



- Up to 48 ON/OFF programmable events
- No neutral required
- Self learning, adapts to your schedule to meet your demands
- Random setting turns lights ON/OFF at different times so it appears someone is always at their home or business
- Controls incandescent lighting
- 15-minute memory guard protects against power failure
- For use with standard or decorator-style wall plate (not included)

<b>Ratings:</b>
<b>Input Voltage:</b> 120 VAC, 60 Hz.
<b>Min. Wattage:</b> 40 W
<b>Max. Wattage:</b> 500 W Incandescent
<b>Inductive Ballast:</b> 4 A
<b>Operating Temperature:</b> 32°F to 104°F (0°C to 40°C)
<b>Warranty:</b> Limited 1 year

Model #	Color
E. EJ351	White

*Not for use with CFL/LED bulb*

## EJ500 Electronic In-Wall Switch Timer



- Versatile 7-Day scheduling
- Up to 14 (7 ON/OFF) programmable events per day
- No neutral required
- Random setting turns lights ON/OFF at different times so it appears someone is always at their home or business
- Auto Daylight Saving Time adjustment
- Astronomic feature auto adjusts to sunrise/sunset
- Controls incandescent lighting
- Battery backup
- Single-pole or 3-way compatible
- For use with decorator-style wall plate (not included)

<b>Ratings:</b>	<b>Tungsten:</b> 4 A
<b>Input Voltage:</b> 120 VAC, 60 Hz.	<b>Inductive Ballast:</b> 4 A
<b>Min. Wattage:</b> 40 W	<b>Operating Temperature:</b> 32°F to 104°F (0°C to 40°C)
<b>Max. Wattage:</b> 500 W Incandescent	<b>Warranty:</b> Limited 1 year

Model #	Color
F. EJ500	White

*Not for use with CFL/LED bulbs*