



ITEM# TI12MC-F



12oz Titanium Milled Face 16” Hybrid Fiberglass Handle Hammer

The STILETTO® 12-Ounce Titanium Milled Face / 16-Inch Hybrid Fiberglass Handle Hammer swings as hard as a 21-ounce steel hammer, making it an ideal choice for almost any framing or remodeling task. With a titanium head that produces 10 times less recoil shock and weighs 45 percent less than comparable steel hammers, this product reduces fatigue and the chance of stress-related injuries. The Stiletto milled face hammer has a strong 16-inch fiberglass handle that provides plenty of reach and leverage. The handle's TPR grip with a thumb divot and curved shape offers all-day comfort at the job site. Stiletto's 12-ounce hammer has a milled face that improves striking accuracy and a straight claw for removing boards or pull nails. It also has a magnetic nail starter built into the head.

INCLUDES:

(1) 12oz Titanium Milled Face 16” Hybrid Fiberglass Handle Hammer (TI12MC-F)

FEATURES:

- 12 Oz Solid Milled face Titanium head
- NEWLY REDESIGNED 16" HYBRID FIBERGLASS HANDLE
- Ergonomic non-slip black TPR grip w/ thumb divot
- Straight claw design
- Stiletto's signature Magnetic Nail Starter

PRODUCT SPECIFICATIONS:

Assembled Weight (lbs)	1.65	MFG Part # (OEM)	TI12MCF
Claw Hammer Type	Curved Claw	Magnetic Nail Set	Yes