

Contender® Series Factory Sealed Control Station Accessories

Explosionproof, Dust-Ignitionproof

UNILETS® for use with Threaded Metal Conduit. Furnished with Internal Ground Screw.

Class I, Division 1, Groups C, D
 Class I, Division 2, Groups B, C, D
 Class II, Division 1 and 2, Groups E, F, G
 Class III
 NEMA 3, 7CD, 9EFG

Nameplates *

Description	Suffix
Mushroom Head Push Buttons (Maintained and Momentary)	
Start	MNPSTQ
Stop	MNPSPQ
Emergency Stop	MNPESTPQ
Blank	MNPBQ
Pilot Light Nameplates	
Blank	LNPBQ
Forward	LNPFDQ
Jog	LNPJOGQ
Run	LNPRUNQ
Stop	LNPSPQ
Start	LNPSTQ
Down	LNPDOWNQ
Fast	LNPFASTQ
Slow	LNPSLOWQ
Raise	LNPRAISEQ
Lower	LNPLOWERQ
Reset	LNPRESETQ
Off	LNPOFFQ
On	LNPONQ
Reverse	LNPREVQ
Close	LNPCLOSEQ
Open	LNPOPENQ
Up	LNPUPQ
Test	LNPTTESTQ
Low	LNPLOWQ
High	LNPHIGHQ
Two Position Selection Switch Nameplates	
Forward-Reverse	SLNPFRQ
Hand—Auto ‡	SLNPHAQ
On—Off	SLNPOO
Start—Stop	SLNPSS
Blank	SLNPBQ
Up—Down	SLNPUDQ
Run—Jog	SLNPRJQ
Auto—Hand	SLNPAHQ
Off—Remote	SLNPORQ
Off—On	SLNPOFON

Description	Suffix
Three Position Selection Switch Nameplates	
Forward—Off—Reverse	SLNPFORQ
Hand—Off—Auto ‡	SLNPHOAQ
Run—Off—Jog	SLNPROJQ
Blank	SLNPB3
Reverse—Off—Forward	SLNPROFQ
Auto—Off—Hand	SLNPAOHQ
Hand—Off—Remote	SLNPHORQ
1—Off—2	SLNP102Q
Jog—Off—Run	SLNPJORQ
Stop—Run—Start	SLNPSRSQ
Local—Off—Remote	SLNPLOEQ
Momentary Push Buttons	
<i>For Rectangular Weatherboot Style Only (not for round weatherboot style)</i>	
Blank †	SNPBQ
Forward	SNPFWDQ
Jog	SNPJOGQ
Run	SNPRUNQ
Stop †	SNPSPQ
Start †	SNPSTQ
Down	SNPDOWNQ
Fast	SNPFASTQ
Slow	SNPSLOWQ
Raise	SNPRAISEQ
Lower	SNPLOWERQ
Reset	SNPRESETQ
Off	SNPOFFQ
On	SNPONQ
Reverse	SNPREVQ
Close	SNPCLOSEQ
Open	SNPOPENQ
Up	SNPUPQ
Test	SNPTTESTQ
Low	SNPLOWQ
High	SNPHIGHQ

* No custom nameplates available.



‡ Included as standard (no need to use suffix).

Contender® Series Factory Sealed Selector Switch Accessories


Explosionproof, Dust-Ignitionproof

10 Amp, 600 Vac Max. for Heavy Duty Use Momentary Contact. Furnished with Internal Ground Screw.

Selector Switches Nameplates

		Two Position Nameplates		Three Position Nameplates	
 <p>Two Position</p>	Forward—Reverse	SLNP-FRQ	Forward—Off—Reverse	SLNP-FORQ	
	Hand—Auto	SLNP-HAQ	Hand—Off—Auto	SLNP-HOAQ	
	On—Off	SLNP-OO	Run—Off—Jog	SLNP-ROJQ	
	Start—Stop	SLNP-SS	Blank	SLNP-B3	
	Blank	SLNP-BQ	Reverse—Off—Forward	SLNP-ROFQ	
 <p>Three Position</p>	Up—Down	SLNP-UDQ	Auto—Off—Hand	SLNP-AOHQ	
	Run—Job	SLNP-RJQ	Hand—Off—Remote	SLNP-HORQ	
	Auto—Hand	SLNP-AHQ	1—Off—2	SLNP-102Q	
	Off—Remote	SLNP-ORQ	Jog—Off—Run	SLNP-JORQ	
	Local Remote	SLNP-LRQ	Stop—Run—Start	SLNP-SRSQ	
	Off—On	SLNP-OFON	Local—Off—Remote	SLNP-LORQ	

Selector Switch Locking Devices — Permit Locking In Any Position

	Description	Catalog Number
	Two or Three Positions	SBL-3-Q

Controls

CONTROLS: HAZARDOUS LOCATION CONTROL STATIONS AND SWITCHES