



NUVO TH315

1-Light MR16 120V Round Back Track Lighting Head

Fixture Type
Track Lighting Heads

Collection
No

Style
Transitional

Finish
White

Width
2.25"

Height
3.25"

Extension
6.5"

Number of Lights
1-Light

Max Wattage
50 Watts

Lamp Type
Halogen

Bulb Type
MR16 Bulb

Bulb Base
GU10 Base

Bulb Included
No

Replaceable Light Source
Yes

Certification
UL Listed

Safety Rated
Dry Location

Energy Saver
No

Energy Star
No

UPC
045923403156

Warranty
1-Year Warranty

Voltage
120 Vots