JB and GS Flexible Fixture Hangers

Malleable Iron. Ball Type, 15° Swing; Cushion Type, 8° Swing

UNILETS® for Use with Threaded Rigid Metal Conduit and IMC.

Applications

- JB, GS and AHG cushion hangers are enclosed and gasketedideal where dust and dampness are present.
- JB and GS hangers designed for use with JB and GS boxes.

Features

- All hangers
 - All fixture hangers protect fixture against wind and vibration damage.
 - Cushion type for added protection where lighting fixtures are subjected to vibration.
- JB and GS hangers
- Mount directly to JB and GS cast conduit outlet boxes. - Choice of ball or cushion type.
- Ball type permits 15° swing, cushion type 8° swing from vertical
- Cushion type is enclosed and gasketed.

Standard Materials

Malleable iron

Standard Finishes

- GS: triple-coat-(1) zinc electroplate, (2) chromate, and (3) epoxy powder coat
- JB series support: zinc electroplate and clear chromate •

Certifications and Compliances

- JB and GS cushion type hangers suitable for classified location use in Class I, Division 2 areas, if installed in compliance with NEC 501-9(b)
- CSA Certified: 065180
- UL Listed: E109438



GSK_50_20B

GSK-50-20C

JBK-50-CS





JB and GS Flexible Fixture Hangers

Malleable Iron. Ball Type, 15° Swing; Cushion Type, 8° Swing UNILETS® for Use with Threaded Rigid Metal Conduit and IMC.

| | Fixture Stem Size (Inches) | Male Nipple Size (Inches) | Length A in/mm | Support Weight (Ibs/kg) | Catalog Number |
|--------------------------------|--|------------------------------|-------------------|----------------------------|-------------------|
| JB—Fixture Hanger Covers — For | use with JBX, JBDX a | and JBLX bodies | s — Furnished wi | th gasket and screws | |
| | Ball Type | | | | |
| | 1/2 | | 2.56/65.0 | 250/113 | JBK-50-BS |
| | 3/4 | | 2.56/65.0 | | JBK-75-BS |
| | Cushion Type |) | | | |
| | Enclosed and gasketed. Cushions 40 lbs./18.0 kg. | | | | |
| | 1/2 | | 1.63/41.4 | 40/18 | JBK-50-CS |
| | 3/4 | | 1.63/41.4 | | JBK-75-CS |
| GS—Fixture Hanger Covers (Form | 20) — For use with G | S and GSU bodi | es — Furnished v | with gasket and screw | S |
| | Ball Type | | | | |
| | 1/2 | | 3.00/76.2 | 250/113 | GSK-50-20E |
| | 3/4 | | 3.25/82.6 | | GSK-75-20E |
| | Cushion Type | • | | | |
| | Enclosed and gasketed. Cushions 40 lbs./18.0 kg. | | | | |
| | 1/2 | | 2.00/50.8 | 40/18 | GSK-50-200 |
| | 3/4 | | 2.00/50.8 | | GSK-75-200 |

1413