



S9226

LED 5.0W G9 450L 3000K
5 watt; T4 Repl. LED; 3000K; G9 base; 360° beam spread; 120 volts

Features

- Solid State LED lighting
- High Efficacy
- Long life
- Omnidirectional light
- Replaces halogen G9 lamps
- Non-Dimmable
- Not for use in totally enclosed fixtures
- Use in dry locations



S9226

Available March 2015

Item Number	UPC	Watts	Lamp Shape	Base	Lamp Code	Voltage	MOL In Inches
S9226	045923092268	5	T4 Replacement	G9	LED 5.0W G9 450L 3000K	120	2 3/8"
Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Incandescent Equivalent	Pack	Package Type
450	15000	3000	Warm White	80	40W	100/20	Box
Beam Spread		RoHS Compliant			UL or ETL Listed		
360		Yes			Yes		



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

