

S9382

6.5MR16/LED/40'/27K/120V/GU10 6.5 watt; LED MR16 LED; 2700K; 40' beam spread; GU10 base; 120 volts

Features

- · Solid State LED lighting
- High Efficacy
- Long life
- Dimmable
- UL approved for totally enclosed fixtures



S9382

Item UPC Number		Voltage	Watts Incandescent Equivalent			Lamp Shape	Base		Lamp	Code	
S9382	045923093821	120	6.5	50W		MR16	GU10	6.5N	6.5MR16/LED/40'/27K/120V/GU10		
Dimmable/	Non-Dimmable	MOL In Inches		IOD In nches	Initial Lu	mens	_	e Rated ours	Kelvin Temp	Color	CRI
Dimmable		2 3/16"		2.00"	500		25	25000		Warm White	80
		Pack I 8/12			RoHS Compliant Yes		iant	nt UL or ETL Listed Yes		Warranty 3 Year Limited	



National Toll-Free: 800.43.SATCO (800.437.2826) www.satco.com Distribution Centers: New York, Florida, Texas, Washington, California, Puerto Rico Corporate Offices: 110 Heartland Blvd., Brentwood, NY 11717 800.437.2826 631.243.2022 Fax 631.243.2027

