

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Lateral Jumper Bars

General Information

Extended Product Type:	PC8-10
Product ID:	1SNA163313R2400
EAN:	3472591633139
Catalog Description:	PC8-10 Lateral Jumper Bars Black
Long Description:	IP20 Comb Jumper bars, - direct insertion in the screw clamp before tightening the screws, above the eventual conductor (if conductor used with ferrule, we recommend the use of long ferrule for optimized mounting ergonomically with test disconnect terminal blocks), - Multiple versions available in pre-cut poles for test disconnect terminal blocks applications.

Ordering

Color:	Black
Minimum Order Quantity:	10 piece
Customs Tariff Number:	39269097

Popular Downloads

Data Sheet, Technical Information:	1SNK160027C0205
Instructions and Manuals:	1SNK160027C0201
Wiring Diagram:	1SNC600151F0000

Dimensions

Product Net Width:	78 mm
Product Net Height:	8 mm
Product Net Depth / Length:	22 mm
Product Net Weight:	14 g

Technical

Spacing:	8 mm
Function:	Lateral Jumper Bars
Rated Current (I_n):	Main Circuit 50 A
Rated Voltage (U_r):	630 V
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide

Suitable For:
C6/8
C6/8.ST4
D6/8.ADO
D6/8.ADO.NC
DB4/8.A.ADO3
DB4/8.ADO
DH4/8.A.ADO
DH4/8.ADO
DR4/8.A.ADO3
DRE4/8.A.ADO3
DS4/8.A.ADO3
DS4/8.ADO
DSE4/8.A.ADO3
DSE4/8.ADO
E6/8
ES8-CG
M6/8
M6/8.2A.G
M6/8.NC
M6/8.S
M6/8.SB
M6/8.SNB
M6/8.ST
M6/8.STP
MS6/8
ZS10-PE-R1
ZS10-R1

Technical UL/CSA

Flammability According to UL94: V0

Environmental

Ambient Air Temperature: Operation -55 ... +110 °C
Storage -55 ... +110 °C

Certificates and Declarations (Document Number)

Declaration of Conformity - CE: 1SND225001C1009

Instructions and Manuals: 1SNK160027C0201

Classifications

Object Classification Code: X

E-nummer: 2925679

ETIM 4: EC000489 - Cross-connector for terminal block

ETIM 5: EC000489 - Cross-connector for terminal block

ETIM 6: EC000489 - Cross-connector for terminal block

Container Information

Package Level 1 Units: 10 piece

Package Level 1 Gross Weight: 0.14 kg

Package Level 1 EAN: 3472591633139

Package Level 2 Units: 500 piece

