

# RAZOR-FR LED FIRE RATED RECESSED DOWNLIGHT



**2 HOUR  
FIRE RATING**

Tested to comply with UL 263,  
ASTM E119 & CAN ULC S101



## FEATURES

- Selectable color temperature:  
3 K, 4 K & 5 K
- Dimmable • Certified airtight • IC rated
- Junction box with driver included
- 50,000 hour lifetime
- Suitable for wet locations



NOMINAL SIZE	MODEL	LIGHT OUTPUT	WATTAGE	LUMINAIRE DIMENSIONS	JUNCTION BOX DIMENSIONS	COLOR TEMPERATURE	CRI
4"	RZR-CCT-FR400	650 LM	10 W	5.06"	3.35" x 3.42" x 1.3"	SELECTABLE 3 K, 4 K ou 5 K	90+
4"	RZR-CCT-FR411	800 LM		5.35"			
6"	RZR-CCT-FR600	950 LM	13 W	7.16"			
6"	RZR-CCT-FR611	1020 LM		7.16"			
6"	RZR-CCT-FR615	1500 LM		7.16"			
LIFETIME 50,000 HOURS		LIGHT DISTRIBUTION BEAM ANGLE 107°		AVAILABLE FINISHES WHITE		LIMITED WARRANTY 5 YEARS	