



LED MR16

7.3MR16/LED/830/F35/DIM 12V 10/1FB

Philips LED MR-16 lamps with single optic technology provide the look and color quality of traditional halogens while using a fraction of the energy. A perfect fit for spot lighting, they are compatible with most existing fixtures with MR16 GU5.3 holders and are designed as a retrofit replacement for halogen or incandescent spots.

Product data

General Information	
Cap-Base	GU5.3 [GU5.3]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	7.3-50W
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	35°
Luminous Flux (Nom)	515 lm
Luminous Intensity (Nom)	1350 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	70.00 lm/W
Color Consistency	<4
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
	<u> </u>
Operating and Electrical	
Input Frequency	- Hz
Power (Rated) (Nom)	7.3 W

Lamp Current (Nom)	830 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	ac electronic 12 V
Temperature	
T-Case Maximum (Nom)	90 ℃
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	7.3MR16/LED/830/F35/DIM 12V 10/1FB


Datasheet, 2021, June 22 data subject to change

LED MR16

EAN/UPC - Product	046677533151
Order code	533158
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10

Material Nr. (12NC)	929001881104
Net Weight (Piece)	0.050 kg


Dimensional drawing




MR16 12V 7-35W 400lm 35D 3000K GU5.3 D

Product D C 7.3MR16/LED/830/F35/DIM 12V 10/1FB 50.5 mm 46.5 mm


Photometric data



LEDspot 7.3W GU5.3 MR16 827 35D DIM




LEDspot 7.3W GU5.3 MR16 830 35D DIM




LEDspot 7.3W GU5.3 MR16 830 25-35D DIM

LED MR16

Lifetime





7-50W GU5-3 MR16

7-50W GU5-3 MR16



© 2021 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.