



LED PAR30 S/L

10PAR30L/LED/830/F25/DIM/ULW/120V 6/1FB

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Product data


General Information	
Cap-Base	E26 [Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	25000X
Technical Type	10-75W
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	25 °
Luminous Flux (Nom)	850 lm
Luminous Intensity (Nom)	3300 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	85.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	10 W
Lamp Current (Nom)	86 mA
Wattage Equivalent	75 W

Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	67 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	PAR30L [PAR 3.75 inch/95mm Long]
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	10PAR30L/LED/830/F25/DIM/ULW/120V 6/1FB
EAN/UPC - Product	046677529710
Order code	529719
Numerator - Quantity Per Pack	1

LED PAR30 S/L

Numerator - Packs per outer box	6
Material Nr. (12NC)	929001321604
Net Weight (Piece)	0.285 kg


Dimensional drawing




Glass UL wet PAR30L 120V 9-75W 850lm 25D

Product	D	C
10PAR30L/LED/830/F25/DIM/ULW/120V 6/1FB	94 mm	118 mm


Photometric data



10-75W E26 PAR30L




10-75W E26 PAR30L 25D 830 3000K



10-75W E26 PAR30L 25D 830 3000K

LED PAR30 S/L

Lifetime



14-120W E26 PAR38

14-120W E26 PAR38

