

D1 Series General Purpose Plug-In Relay

D1PF1AT

UPC:786685270005

Dimensions:

- **Height:** 1.1 IN
- **Length:** 1.6 IN
- **Width:** .53 IN

Weight:.1 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Coil Voltage:** 24V
- **Contact Configuration:** SPDT
- **Contact Material:** Silver alloy
- **Contact Rating:** 20A
- **Cover:** Full featured
- **Enclosure:** IP40
- **Frequency Rating:** 50-60 Hz
- **Maximum Voltage:** 300V switching
- **Options:** Locking pushbutton, bipolar LED, removable ID tag, mechanical flag indicator
- **Resistance:** 180 Ohms
- **Series:** D1 series
- **Terminals:** Plug-in

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [D1_F1 2D Drawing Xchange](#)
- [D1_F1 AutoCAD 2D Footprint \(mm\)](#)
- [D1_F1 AutoCAD 2D Footprint](#)
- [D1_F1 2D PDF](#)

- [D1_F1 3D Model Xchange](#)
- [Eaton Specification Sheet - D1PF1AT](#)

Certifications:

- cRUus
- UL Listed
- CSA Certified

Product compliance:

- RoHS Compliant
- CE Marked

© 2016 Eaton. All rights reserved.