



SKU: CSWS-2/0-38

UPC: 0783669637052

Features & Benefits:

Description: Surecrimp Copper Compression Lug, Conductor Size 2/0, 1 Hole, 3/8in Bolt Size, Standard Barrel, Sight Window, Tin Plated, UL, CSA

Specs

Additional Class Attributes

Barrel Marking	Ink
Barrel Type	Standard
Connecting Angle	180°
Connection	Compression
Contains DE-OX®	No
Flared End	No
ILSCOs Die Catalog Number	ILD-45
ILSCOs Die Index Number	I-45
Mounting Hole Type	Thru
Narrow Tang	No
Number of Mounting Holes	1
Sight Window	Yes
Slotted	No
Tang End Shape	Square
Undrilled	No

Dimensions

Barrel Length (IN)	0.85
Barrel Length (mm)	21.59
Dimension G (IN)	0.414
Dimension G (mm)	10.5156
Height (IN)	0.597
Height BX (IN)	2.25
Height (mm)	15.1638
Inside Diameter (IN)	0.437
Inside Diameter (mm)	11.0998
Length (IN)	2.121
Length (mm)	53.8734
Mounting Bolt/Stud Size (mm)	965.2
Mounting Hole Diameter (IN)	0.406
Mounting Hole Diameter (mm)	10.3124
Mounting Hole Spacing (mm)	0
Outside Diameter (IN)	0.562
Outside Diameter (mm)	14.2748
Strip Length (mm)	20.6248
Tang Length (IN)	0.875
Tang Length (mm)	22.225
Tang Thickness (IN)	0.125
Tang Thickness (mm)	3.175

Tang Width (IN)	0.811
Tang Width (mm)	20.5994
Weight (LB)	0.0604460920218473
Weight BX (LB)	1.486
Width (IN)	0.811
Width BX (IN)	5
Width (mm)	20.5994

Conductor Ranges

Conductor Range AL Stranded (Primary, run, main, line)	NA
Conductor Range CU Solid (Primary, run, main, line)	NA
Conductor Range CU Stranded (Primary, run, main, line)	2/0 Str
Conductor Range AL Solid (Primary, run, main, line)	NA
Expanded Conductor Range	2/0 Str - 4 Str
Flex Conductor Range	1/0 G,H,I,K,M,DLO

Material and Finish

Conductor Material	Copper
Connector Finish	Tin
Insulation	NA
Material	Copper

Additional Technical Specifications

Conductor Type	Flex
----------------	------

General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 10
Direct Burial	Yes
Dual Rated	No
NEMA Code	S-588-3
UPC Code	78366963705

Bolt and Screw Sizes

Mounting Bolt/Stud Size	3/8
-------------------------	-----

Testing Standards

CSA File Number	LR-29601
CSA Standard	C22.2 No. 65-03
NEBS Rating	Level 3
Prop65 Compliance	This product is in compliance with Prop65. It is not known to contain any chemicals associated with this regulation
UL Control Number	453G
UL / CULUS Specification	UL 486A/B Listed
UL File Number	E6207

Environment and Temperature

Temperature Rating

90°C

Color

Color

Silver

Color Code

Black

Voltage

Voltage Rating

35 kV