



**SKU:** ASN-1/0

**UPC:** 0783669184761

**Features & Benefits:**

**Description:** Surecrimp Aluminum Compression Sleeve, Conductor Size 1/0, Tin Plated, UL, CSA

## Specs

### Additional Class Attributes

Barrel Marking	Hard
Barrel Type	Standard
Connecting Angle	180°
Connection	Compression
Contains DE-OX®	Yes
Flared End	No
ILSCOs Die Index Number	296
Number of Conductors	1
Sight Window	No
Slotted	No

### Dimensions

Height (IN)	0.599
Height BX (IN)	2.25
Height (mm)	15.2146
Inside Diameter (IN)	0.385
Inside Diameter (mm)	9.779
Length (IN)	2.573
Length (mm)	65.3542
Outside Diameter (IN)	0.599
Outside Diameter (mm)	15.2146
Weight (LB)	0.041
Weight BX (LB)	0.5071
Width (IN)	0.599
Width BX (IN)	5
Width (mm)	15.2146

### Conductor Ranges

Conductor Range AL Stranded (Primary, run, main, line)	1/0 Str
Conductor Range CU Solid (Primary, run, main, line)	NA
Conductor Range CU Stranded (Primary, run, main, line)	1/0 Str
Conductor Range AL Solid (Primary, run, main, line)	NA
Expanded Conductor Range	1/0 Str - 1 Str
Flex Conductor Range	NA

### Material and Finish

Conductor Material	Aluminum
Connector Finish	Tin
Material	Aluminum

### Additional Technical Specifications

Conductor Type	Stranded
----------------	----------

### General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 10
Dual Rated	Yes
NEMA Code	S-588-1
UPC Code	78366918476

### Bolt and Screw Sizes

Mounting Bolt/Stud Size	NA
-------------------------	----

### Testing Standards

CSA File Number	LR-29601
CSA Standard	C22.2 No. 65-03
Prop65 Compliance	This product is in compliance with Prop65. It is not known to contain any chemicals associated with this regulation
UL Control Number	453G
UL / CULUS Specification	UL 486A/B Listed
UL File Number	E6207

### Environment and Temperature

Temperature Rating	90°C
--------------------	------

### Color

Color	Silver
Color Code	Tan

### Voltage

Voltage Rating	35 kV
----------------	-------