



SKU: ASN-2/0

UPC: 0783669184778

Features & Benefits:

Description: Surecrimp Aluminum Compression Sleeve, Conductor Size 2/0, Tin Plated, UL, CSA

Specs

Additional Class Attributes

Barrel Marking	Hard
Barrel Type	Standard
Connecting Angle	180°
Connection	Compression
Contains DE-OX®	Yes
Flared End	No
ILSCOs Die Index Number	297
Number of Conductors	1
Sight Window	No
Slotted	No

Dimensions

Height (IN)	0.674
Height BX (IN)	2.25
Height (mm)	17.1196
Inside Diameter (IN)	0.432
Inside Diameter (mm)	10.9728
Length (IN)	2.71
Length (mm)	68.834
Outside Diameter (IN)	0.674
Outside Diameter (mm)	17.1196
Weight (LB)	0.055
Weight BX (LB)	0.6471
Width (IN)	0.674
Width BX (IN)	5
Width (mm)	17.1196

Conductor Ranges

Conductor Range AL Stranded (Primary, run, main, line)	2/0 Str
Conductor Range CU Solid (Primary, run, main, line)	NA
Conductor Range CU Stranded (Primary, run, main, line)	2/0 Str
Conductor Range AL Solid (Primary, run, main, line)	NA
Expanded Conductor Range	2/0 Str - 1 Str
Flex Conductor Range	NA

Material and Finish

Conductor Material	Copper
Connector Finish	Tin
Material	Aluminum

Additional Technical Specifications

Conductor Type	Stranded
----------------	----------

General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 10
Dual Rated	Yes
NEMA Code	S-588-1
UPC Code	78366918477

Bolt and Screw Sizes

Mounting Bolt/Stud Size	NA
-------------------------	----

Testing Standards

CSA File Number	LR-29601
CSA Standard	C22.2 No. 65-03
Prop65 Compliance	This product is in compliance with Prop65. It is not known to contain any chemicals associated with this regulation
UL Control Number	453G
UL / CULUS Specification	UL 486A/B Listed
UL File Number	E6207

Environment and Temperature

Temperature Rating	90°C
--------------------	------

Color

Color	Silver
Color Code	Olive

Voltage

Voltage Rating	35 kV
----------------	-------