

Tmax XT ranges

XT1 Accessories

3



EF terminal



FCCu terminal

Terminals

Type	3 pcs Part number	4 pcs Part number	6 pcs Part number	8 pcs Part number
F Front terminals	KXT1F-3PC	KXT1F-4PC	KXT1F-6PC	KXT1F-8PC
F Front terminals for MCP	KXT1F3PCMCP	-	KXT1F6PCMCP	-
EF Extended front terminals	KXT1EF-3PC	KXT1EF-4PC	KXT1EF-6PC	KXT1EF-8PC
ES Extended spread terminals	KXT1ES-3PC	KXT1ES-4PC	KXT1ES-6PC	KXT1ES-8PC
FC Cu Terminals for Cu cables 125A, 14-1/0 AWG, 1x2.5...50mm ²	KXT1CU-3PC	KXT1CU-4PC	KXT1CU-6PC	KXT1CU-8PC
FC Cu Terminals for Cu cables MCP, 14-1/0 AWG, 1x1.5...50mm ²	KXT1CUMCP-3PC	KXT1CUMCP-4PC	KXT1CUMCP-6PC	KXT1CUMCP-8PC
MC Multi cable terminals for Cu cables, 6x14-2 AWG, 6x2.5...35mm ²	KXT1MC-3PC	KXT1MC-4PC	KXT1MC-6PC	KXT1MC-8PC
R Rear adjustable terminals ⁽¹⁾	KXT1ER-3PC	KXT1ER-4PC	KXT1ER-6PC	KXT1ER-8PC
R -RC Rear terminals for residual current ⁽¹⁾	-	KXT1ERRC-4PC	-	-
FB Flexibar Terminals ⁽¹⁾	KXT1EFB-3PC	KXT1EFB-4PC	KXT1EFB-6PC	KXT1EFB-8PC

⁽¹⁾IEC rated only.

Automatic transfer devices

ATS021 - ATS022 Automatic transfer devices⁽¹⁾

Type	Part number
ATS021	ATS021
ATS022	ATS022

⁽¹⁾IEC rated only.



ATS021

Spare parts

Type	Part number
SA RC Sel / RC Inst - Opening solenoid for the residual current device ⁽¹⁾	KXT1ESARCFP
AUX-C - Loose cabled auxiliary contact 250V AC ⁽²⁾	KXTAAUXCFP
AUX-C - Loose cabled auxiliary contact 24V DC ⁽²⁾	KXTAAUXCDFP
AUX-C - Loose cabled auxiliary contact 250V AC 600V ⁽²⁾	KXTAAUXCFPHD
AUX-C - Loose cabled auxiliary contact 24V DC 600V ⁽²⁾	KXTAAUXCDFPHD

⁽¹⁾IEC rated only.

⁽²⁾Un-numbered cables.

Flanges for the compartment door⁽¹⁾

Type	3p Part number	4p Part number
Small "optional" flange for circuit breaker	KXTAEFLASMFP	KXTAEFLASMFP
Large "standard" flange for circuit breaker	KXT1EFLAFP-3	KXT1EFLAFP-4
Flange for MOD	KXTBEFLAMOD	KXTBEFLAMOD
Flange for direct handle RHD	KXTAEFLARHDFP	KXTAEFLARHDFP
Flange for residual current RC Sel/RC Sel	KXT1EFLARCFP-3	KXT1EFLARCFP-4

⁽¹⁾IEC rated only.



Flange