

Round retrofit LED panel light

The aluminum retrofit LED panel offers the easiest and most practical solution to your existing lighting needs. For style and convenience, the removable outer trim attaches with magnetic fasteners to create a seamless look. Can be easily retrofitted in existing 4" canisters or standard octagonal junction boxes.



Model	Size	Watts	Delivered lumens	LED lumens	CRI	Color °T	Voltage
RTF4-3K	4"	9 W	550 lm	630 lm	90	3000 K	120 V

Specifications

Fits on octagonal junction boxes
 Includes A-19 socket
 Fits into 4" recessed housings
 Minimal heat emission
 Aluminum construction
 Over 50,000 hours of service life
 Magnetic trim finish
 Suitable for wet locations
 Refer to website for dimmer compatibility
 Ideal operating temperature:
 -20° to 40° C
 5-year warranty

Note

Other Color °T and Finishes available, but may require MOQ's and longer lead times. Please contact your DALs representative for more information.

Finish

- **BK** Black
- **SN** Satin Nickel
- **WH** White

Order example

RTF4-3K-BK
 Black 4" retrofit panel light with 550 Lumens at 3000 K

RTF4-3K

