

Project Name

Location

Prepared By



SATCO S11251

4.5G25/LED/TW/CL/SF

Notes

[www] 03-09-2021 01:43:25

General

Status	Active
Watts	4.5
Incandescent Equivalent	40
Volts	120V
Shape	G25
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	2700K-5000K
Temperature	Warm to Cool White
CRI	80
Lumens	450
Beam Spread	220
Dimmable	Dimmable Only with Starfish App
Hours Rated	15000
Lamp Type	Globe
Technology	LED

Smart Product Info

IOT Enabled	Yes
Voice Assistants Supported	Siri Shortcuts; Alexa; Hey Google; SmartThings

Electrical

Operating Frequency	60 Hz
---------------------	-------

Specifications

Dimming Type	Smart
Power Factor	0.5
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	4.45
MOD	3.15
Weight (lb.)	0.11

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 3 hr per day

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
California Status	Non-Compliant
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

