

Project Name

Location

Prepared By



SATCO S11252

9.5A19/LED/RGB/TW/SF

Notes

[www] 03-22-2021 04:50:55

General

Status	Active
Watts	9.5
Incandescent Equivalent	60
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	White
CCT (Kelvin)	2700K-5000K
Temperature	Warm to Cool White
CRI	80
Lumens	800
Beam Spread	220
Dimmable	Dimmable Only with Starfish App
Hours Rated	25000
Lamp Type	Type A
Technology	LED

Smart Product Info

IOT Enabled	Yes
Voice Assistants Supported	Siri; Alexa; Hey Google; SmartThings

Electrical

Operating Frequency	60 Hz
---------------------	-------

Specifications

Dimming Type	Smart
Power Factor	0.6
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	4.57
MOD	2.36
Housing Color	White
Weight (lb.)	0.15

Additional Information

Rated For Enclosed Fixture	No
Warranty	3 Year Limited - 3 hr per day

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2368811
California Status	Non-Compliant
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes



FCC Compliant	Yes
SDS Sheet	LED_Lamp

