

Project Name

Location

Prepared By



Notes

[www] 03-22-2021 04:50:55

General

Status	Active
Watts	9.5
Incandescent Equivalent	65
Volts	120V
Shape	BR30
Base	Medium
ANSI Base	E26
Finish	White
CCT (Kelvin)	2700K-5000K
Temperature	Warm to Cool White/Color Changeable
CRI	80
Lumens	800
Beam Spread	100
Dimmable	Dimmable Only with Starfish App
Hours Rated	25000
Lamp Type	Reflector
Technology	LED

Smart Product Info

IOT Enabled	Yes
Voice Assistants Supported	Siri; Alexa; Hey Google; SmartThings

Electrical

Operating Frequency	60 Hz
---------------------	-------

Specifications

Dimming Type	Smart
Power Factor	0.6
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	5.12
MOD	3.70
Weight (lb.)	0.21

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 3 hr per day

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2368817
California Status	Non-Compliant
California Compliant Substitute	S11276
Nevada Status	Lawful for sale in Nevada



RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

