

Project Name

Location

Prepared By



SATCO S11258

15PAR38/LED/RGB/TW/SF

Notes

[www] 03-15-2021 00:27:51

General

Status	Active
Watts	15
Incandescent Equivalent	90
Volts	120V
Shape	PAR38
Base	Medium
ANSI Base	E26
Finish	White
CCT (Kelvin)	2700K-5000K
Temperature	Warm to Cool White/Color Changeable
CRI	80
Lumens	1200
Beam Spread	40
Dimmable	Dimmable Only with Starfish App
Hours Rated	25000
Lamp Type	PAR
Technology	LED

Smart Product Info

IOT Enabled	Yes
Voice Assistants Supported	Siri; Alexa; Hey Google; SmartThings

Electrical

Operating Frequency	60 Hz
---------------------	-------

Specifications

Dimming Type	Smart
Power Factor	0.9
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	5.00
MOD	4.72
Lens Finish	Clear
Lens Material	Plastic
Weight (lb.)	0.33

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 3 hr per day

Compliance

Safety Listing	cULus
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2368909
California Status	Non-Compliant

California Compliant Substitute	S11277
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

