

Project Name

Location

Prepared By



SATCO S11259

8.7W/LED/RDL/4/TW/T20/JA8/SF

Notes

[www] 03-22-2021 04:50:55

General

| | |
|---------------------------|--------------------|
| Status | Active |
| Finish | White |
| Wattage | 8.7 |
| CCT (Kelvin) | 2700K-5000K |
| Color Temperature | Warm to Cool White |
| Width (in.) | 5.12 |
| Height (in.) | 2.80 |
| Indoor or Outdoor Fixture | Indoor |

Smart Product Info

| | |
|----------------------------|--|
| IOT Enabled | Yes |
| Voice Assistants Supported | Siri Shortcuts; Alexa; Hey Google; SmartThings |

Specifications

| | |
|-----------------------|---|
| Technology | LED |
| CRI | 90 |
| Lumen Output | 700 |
| Rated Hours | 25000 |
| Voltage | 120V |
| Dimmable | Dimmable Only with Starfish App |
| Recommended Dimmer | Smart |
| Beam Angle | 90 |
| Operating Temperature | -20C (-4F) to a maximum of +45C (+113F) |
| IC Rated | Yes |
| Weight (lb.) | 0.34 |
| Fixture Shape | Round |
| Fixture Material | Metal |
| Fixture Type | Downlight Retrofit |

Compliance

| | |
|--------------------|--------------------------------|
| Safety Listing | cULus Classified; cULus Listed |
| Location Rating | Wet |
| Energy Star | Yes |
| ES Unique ID | ESID-2371661 |
| California Status | California T24 Compliant |
| California Prop 65 | Lead |
| RoHS Compliant | Yes |
| FCC Compliant | Yes |

Additional Information

| | |
|----------|-------------------------------|
| Includes | E26 Adapter |
| Warranty | 5 Year Limited - 3 hr per day |