SATCO' NUVO

Project Name

Location

Prepared By



SATCO S11261

10WLED/DW/4"/TW/RD/SF

Notes

wwwi 03-22-2021 04:50:55

Status	Active
Finish	White
Wattage	10
CCT (Kelvin)	2700K-5000K
Color Temperature	Warm to Cool White
Width (in.)	5.31
Height (in.)	1.50
Indoor or Outdoor Fixture	Indoor
Smart Product Info	
IOT Enabled	Yes
Voice Assistants Supported	Siri Shortcuts; Alexa; Hey Google SmartThings
Specifications	
Technology	LED
CRI	80
Lumen Output	650
Rated Hours	25000
Voltage	120V
Dimmable	Dimmable Only with Starfish App
Recommended Dimmer	Smart
Beam Angle	110
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
IC Rated	Yes
Weight (lb.)	0.81
Fixture Shape	Round
Fixture Material	Steel
Fixture Type	Remove Driver LED Downlight
Compliance	
Safety Listing	cETLus
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2371663
California Compliant Substitute	S11279
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Warranty

5 Year Limited - 3 hr per day

For More Information Visit: <u>https://www.satco.com/</u>

