

Project Name

Location

Prepared By



Notes

[www] 03-15-2021 00:27:51

General

Status	Active
Finish	White
Wattage	12
CCT (Kelvin)	2700K-5000K
Color Temperature	Warm to Cool White
Width (in.)	7.20
Height (in.)	1.50
Indoor or Outdoor Fixture	Indoor

Smart Product Info

IOT Enabled	Yes
Voice Assistants Supported	Siri Shortcuts; Alexa; Hey Google; SmartThings

Specifications

Technology	LED
CRI	80
Lumen Output	850
Rated Hours	25000
Voltage	120V
Dimmable	Dimmable Only with Starfish App
Recommended Dimmer	Smart
Beam Angle	110
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
IC Rated	Yes
Weight (lb.)	1.03
Fixture Shape	Round
Fixture Material	Steel
Fixture Type	Remove Driver LED Downlight

Compliance

Safety Listing	cETLus
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2371664
California Compliant Substitute	S11280
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Warranty	5 Year Limited - 3 hr per day
----------	-------------------------------