

Project Name

Location

Prepared By



SATCO S11273

1S14/LED/RGBW/12V/SF/2PK

Notes

[www] 03-15-2021 00:27:51

General

Status	Active
Watts	1
Incandescent Equivalent	15
Volts	12V
Shape	S14
Base	4-PIN
ANSI Base	4-PIN
Finish	Black
CCT (Kelvin)	2700
Temperature	Warm White & RGBW Color Changing
CRI	80
Lumens	26
Beam Spread	120
Dimmable	Dimmable Only with Starfish App
Hours Rated	15000
Lamp Type	String Light
Technology	LED

Electrical

Dimming Type	Smart
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	3.46
MOD	1.77
Weight (lb.)	0.05

Additional Information

Additional Info	Replacement Lamp for S11272
Warranty	3 Year Limited - 3 hr per day

Compliance

Safety Listing	cULus
Location Rating	Wet
Energy Star	No
California Status	Lawful for sale in California
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
SDS Sheet	LED_Lamp