

Project Name

Location

Prepared By



NUVO 65-750

LED SMALL 20W ROUND WALL PACK

Notes

[www] 01-25-2021 01:02:05

General

Status	Active
Fixture Type	Area Light
Finish	Black
Wattage	20
Lumen Output	2600L - 2800L
CCT (Kelvin)	3000K/4000K/5000K
IP Rating	IP65
Indoor or Outdoor Fixture	Outdoor

Specifications

Technology	LED
CRI	80
Voltage	120V-277V
Beam Angle	100
Rated Hours	50000
Operating Temperature	-30C (-22F) to a maximum of +45C (+113F)
Dimmable	Yes - Dimmable
Photocell	Yes - Bypassable
Surge Protection	Built-in surge protection - 2.5KV
Weight (lb.)	2.42
Material	Die-cast Aluminum

Dimensions

Height (in.)	8.70
Extension (in.)	3.40

Compliance

Safety Listing	cULus
Location Rating	Wet
DLC Approved	Yes
DLC ID	PLGEPXY78U37
California Status	California T24 Compliant
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Additional Information	UV stabilized powder coated finish
Warranty	5 Year Limited - Fixtures